












# VISSERIE

→ VISSERIE		Emb.	GS	EZ	Emb.	HR	Emb.	304L	Emb.	316L
Boulons poêlier avec écrous - BTRCC 	<b>BTRCC 6 X 12</b>	Sac 100 P	-	<b>801 001</b>	50 P	350 401	Sac 100 P	801 008	-	801 004
	<b>BTRCC 6 X 20</b>	Sac 100 P	-	<b>801 011</b>	50 P	350 402	Sac 100 P	801 018	-	801 014
	<b>BTRCC 6 X 30</b>	Sac 100 P	-	<b>801 021</b>	50 P	350 403	-	-	-	-
	<b>BTRCC 8 X 20</b>	Sac 100 P	-	-	50 P	-	-	-	-	<b>801 034</b>
Boulons poêlier avec écrous - BTRL 	<b>BTRL 6 X 12</b>	Sac 100 P	-	<b>801 101</b>	-	-	-	-	-	-
	<b>BTRL 8 X 15</b>	Sac 100 P	-	801 111	-	-	-	-	-	-
Tiges filetées 	<b>TF 6 X 1000</b>	50 P	-	<b>801 701</b>	20 P	350 456	1 P	-	-	801 704
	<b>TF 8 X 1000</b>	25 P	-	<b>801 711</b>	20 P	350 457	1 P	-	-	801 714
	<b>TF 10 X 1000</b>	20 P	-	801 721	20 P	350 458	1 P	-	-	801 724
	<b>TF 12 X 1000</b>	10 P	-	801 731	10 P	350 459	1 P	-	-	801 734
	<b>ST FPU</b>	10 P	<b>350 578</b>	-	-	-	-	-	-	-
Manchons taraudés 	<b>MF 6 X 20</b>	Sac 50 P	-	<b>801 741</b>	50 P	350 430	-	-	-	-
	<b>MF 8 X 20</b>	Sac 50 P	-	801 751	50 P	350 431	-	-	-	-
	<b>MF 10 X 30</b>	Sac 50 P	-	801 771	50 P	350 432	-	-	-	-
	<b>MF 12 X 30</b>	Sac 50 P	-	801 761	50 P	350 433	-	-	-	-
Écrous à embase crantée 	<b>EEC M6</b>	Sac 100 P	-	<b>801 201</b>	50 P	350 405	-	-	Sac 100 P	801 204
	<b>EEC M8</b>	Sac 100 P	-	<b>801 211</b>	50 P	350 406	-	-	Sac 50 P	801 214
	<b>EEC M10</b>	Sac 100 P	-	801 221	50 P	350 407	-	-	Sac 50 P	801 224
	<b>EEC M12</b>	Sac 100 P	-	801 231	50 P	350 408	-	-	Sac 50 P	801 234
Écrous frein - EE8NYL 	<b>EE8NY</b>	Sac 100 P	-	-	-	801 243	-	-	-	-
Écrous hexagonaux 	<b>HM 6</b>	Sac 50 P	-	<b>801 061</b>	50 P	350 410	-	-	-	-
	<b>HM 8</b>	Sac 100 P	-	801 611	50 P	350 411	-	-	Sac 100 P	801 614
	<b>HM 10</b>	Sac 100 P	-	801 621	50 P	350 412	-	-	Sac 100 P	801 624
	<b>HM 12</b>	Sac 100 P	-	<b>801 631</b>	50 P	350 413	-	-	Sac 100 P	801 634
Rondelles carrossier et plates 	<b>RCM6</b>	50 P	-	-	-	350 416	-	-	-	-
	<b>RCM8</b>	50 P	-	-	-	350 417	-	-	-	-
	<b>RCM10</b>	50 P	-	-	-	350 418	-	-	-	-
	<b>RCM12</b>	50 P	-	-	-	350 419	-	-	-	-
	<b>RM6</b>	Sac 100 P	-	801 501	50 P	350 420	-	-	-	801 504
	<b>RM8</b>	Sac 100 P	-	<b>801 511</b>	50 P	350 421	-	-	-	801 514
	<b>RM10</b>	Sac 100 P	-	801 521	50 P	350 422	-	-	-	801 524
	<b>RM12</b>	Sac 100 P	-	<b>801 531</b>	50 P	350 423	-	-	-	801 534
Vis à tête hexagonale 	<b>VHM 5 X 60</b>	Sac 1 P	-	<b>341 728</b>	-	-	-	-	-	-
	<b>VHM 6 X 12</b>	-	-	-	50 P	350 436	-	-	-	-
	<b>VHM 6 X 20</b>	Sac 100 P	-	801 301	50 P	350 437	50 P	-	-	<b>801 304</b>
	<b>VHM 8 X 20</b>	Sac 100 P	-	<b>801 321</b>	50 P	350 438	-	-	Sac 100 P	801 324
	<b>VHM 8 X 25</b>	Sac 100 P	-	801 331	50 P	-	-	-	-	-
	<b>VHM 8 X 30</b>	Sac 100 P	-	-	50 P	350 440	-	-	-	-
	<b>VHM 8 X 40</b>	Sac 100 P	-	801 341	50 P	350 441	-	-	-	801 344
	<b>VHM 8 X 60</b>	Sac 100 P	-	-	50 P	350 442	-	-	-	-
	<b>VHM 10 X 20</b>	Sac 100 P	-	801 361	50 P	-	-	-	-	-
	<b>VHM 10 X 25</b>	Sac 50 P	-	<b>801 371</b>	50 P	350 439	-	-	-	801 374
	<b>VHM 10 X 70</b>	Sac 100 P	-	801 431	50 P	350 443	-	-	-	-
	<b>VHM 12 X 25</b>	Sac 100 P	-	801 401	50 P	350 444	Sac 100 P	-	-	801 404
	<b>VHM 12 X 30</b>	Sac 100 P	-	801 411	50 P	-	Sac 100 P	-	-	801 414
	<b>VHM 12 X 50</b>	Sac 100 P	-	801 421	50 P	350 445	Sac 100 P	-	-	801 424
<b>VHM 12 X 70</b>	Sac 50 P	-	801 461	50 P	350 446	Sac 50 P	-	-	801 464	
<b>VHM 12 X 110</b>	Sac 50 P	-	801 471	50 P	350 447	Sac 50 P	-	-	801 474	
Écrous E41 	<b>E41 M6</b>	Sac 100 P	-	801 801	100 P	350 448	Sac 100 P	-	-	801 804
	<b>E41 M8</b>	Sac 100 P	-	<b>801 811</b>	100 P	350 449	Sac 100 P	-	-	801 814
	<b>E41 M10</b>	Sac 100 P	-	801 821	100 P	350 450	-	-	-	-
	<b>E41 M12</b>	Sac 100 P	-	<b>801 831</b>	100 P	350 451	Sac 100 P	-	-	801 834
Écrous E41RC (pour rail 41 x 21) 	<b>E41RC M6</b>	Sac 100 P	-	801 841	-	-	-	-	-	-
	<b>E41RC M8</b>	Sac 100 P	-	801 851	-	-	-	-	-	-
	<b>E41RC M10</b>	Sac 100 P	-	801 861	-	-	-	-	-	-
	<b>E41RC M12</b>	Sac 100 P	-	801 871	-	-	-	-	-	-