

floor grommets

access / power and data



EG0010




EG0030



EG0040



EG0045

 Dimensions and technical information p. 37

Pack	Cat. Nos.	Plastic access grommets
1	EG0010	<p>Quick fit installation Precision engineered from hard wearing durable ABS Grey mouldings. Other colours available to special order Conform to BS EN 61534-22 Simply secured by pushing down the spring-loaded screws and rotating a quarter turn Recommended for use in light traffic areas Avoid positioning in walkways or under static loads</p> <p>144 mm Ø – cut-out size 127 mm Ø Can accommodate all cable types or three metal conduits up to a 20 mm Ø or 25 mm without foam</p>
1	EG0030	<p>169 mm Ø – cut-out size 152 mm Ø Allows power, data and flexible conduit up to 32 mm to pass through raised access floor Lid can be locked with screw (included) Maximum number of conduits : 9 x 20 mm Ø 5 x 25 mm Ø 3 x 32 mm Ø</p>
1	EG0055	<p>232 mm Ø – cut-out size 215 mm Ø High capacity grommet Recommended for installation in light traffic areas Maximum number of conduits : 18 x 20 mm Ø 10 x 25 mm Ø 6 x 32 mm Ø</p>

Pack	Cat. Nos.	Aluminium access grommet
1	EG0015	<p>Body – cast aluminium Lid – injection moulded plastic Nylon 66 with neoprene cable gasket Secured by quarter-turn fasteners Floor depth 25 to 55 mm Access grommet depth 60 mm (95 mm when back box included)</p> <p>144 mm Ø – cut-out size 127 mm Ø Allows power, data and flexible conduit up to 25 mm to pass through raised access floor</p>

Pack	Cat. Nos.	Aluminium power grommet
1	EG0025	<p>For information on knockout sizes p. 37</p> <p>13 A power grommet Supplied complete with 13 A switched socket</p>

Pack	Cat. Nos.	Plastic power and data grommets
1	EG0040	<p>169 mm Ø – cut-out size 152 mm Ø Quick fit installation Precision engineered from hard wearing durable ABS Grey mouldings. Other colours available to special order. Conform to BS EN 61534-22 Removable carpet recess Cable flap feature so grommet lid can be closed while in use Simply secured by pushing down the spring-loaded screws and rotating a quarter turn Recommended for use in light traffic areas Avoid positioning in walkways or under static loads For information on knockout sizes p. 37</p> <p>13 A power grommet Supplied complete with 13 A unswitched socket</p>
1	EG0045	<p>RCD 30 mA switched socket power grommet Supplied complete with 13 A RCD 30 mA switched socket passive</p>
1	EG0051	<p>13 A power/data grommet Supplied complete with 13 A socket and 1 x 37 x 22 mm cut-out</p>
1	EG0052	<p>Data grommet Supplied complete with data plate 2 x 37 x 22 mm cut-out No knockout</p>
1	EG0053	<p>Cleaners floor grommets 169 mm Ø Non-standard 5 A socket</p>
1	EG0035	<p>Single switched socket</p>

Pack	Cat. Nos.	Pre-wired power grommets
		<p>Recommended for use in light traffic areas For information on knockout sizes p. 37</p> <p>169 mm Ø – cut-out size 152 mm Ø</p> <p>Cleaners socket version</p>
1	EG0041	DP1332 - 3 m unfused
1	EG0042	DP1532 - 5 m unfused
1	EG0043	DP1313 - 3 m 13 A fused
1	EG0044	DP1513 - 5 m 13 A fused
		RCD 30 mA switched socket version
1	EG0046	DP1332 - 3 m unfused
1	EG0047	DP1532 - 5 m unfused
1	EG0048	DP1313 - 3 m 13 A fused
1	EG0049	DP1513 - 5 m 13 A fused

 Please consult us for IP 66 assembled fixed or hinged lid grommets with power and data sockets
contact us on +44 (0) 370 608 9020

