

Intersoc-R™ desk modules

protection, BS sockets, end caps and interlinks



IAC502R



IAB402A



IAZ001A



IAB703A



IAB533F



IAB450A



IAB610B



IAB600B



IAB504R

 Dimensions and technical information **p. 44-47**

The BS version is available with fixed or rotatable sockets. Individually fused sockets are available to meet the requirements of BS 6396 + A1 (5 x 20 mm anti-surge ceramic fuses)
A wide range of interconnection solutions are available. When 16 A cabling interconnection is used with 32 A under-desk solutions, suitable de-rating protection devices must be incorporated to protect the cables
All protection and switching modules, end caps and interlinks are universally compatible with standard and clean earth / low noise systems

Pack	Cat. Nos.	Protection and switching modules
1	IAB401A	With 13 A fuse
1	IAB402A	With 13 A fuse and sw/neon
1	IAB403A	With 13 A fuse and neon
1	IAB404A	32 A max. single isolation module
1	IAB405A	With RCD 30 mA – AC type
1	N IAB405AA	With RCD 30 mA – A type
1	IAB408A	With neon indicator
1	IAB420A	With 16 A MCB
1	IAB430A	With 20 A MCB
1	IAB440A	With 32 A MCB
1	IAB450A	With 16 A RCBO 30 mA – AC type
1	N IAB450AA	With 16 A RCBO 30 mA – A type
1	IAB460A	With 20 A RCBO 30 mA – AC type
1	N IAB460AA	With 20 A RCBO 30 mA – A type
1	IAB470A	With 32 A RCBO 30 mA – AC type
1	N IAB470AA	With 32 A RCBO 30 mA – A type

Pack	Cat. Nos.	Socket modules – standard (grey sockets)
1	IAB502F	2 gang unfused Fixed sockets
1	IAB502R	Rotatable sockets
1	IAB532F	2 gang individually fused 3-15 A – fixed sockets
1	IAB532R	3-15 A – rotatable sockets
1	IAB503F	3 gang unfused Fixed sockets
1	IAB503R	Rotatable sockets
1	IAB533F	3 gang individually fused 3-15 A – fixed sockets
1	IAB533R	3-15 A – rotatable sockets
1	IAB504F	4 gang unfused Fixed sockets
1	IAB504R	Rotatable sockets
1	IAB534F	4 gang individually fused 3-15 A – fixed sockets
1	IAB534R	3-15 A – rotatable sockets

Pack	Cat. Nos.	Socket modules – low noise / clean earth (green sockets)
1	IAC502F	2 gang unfused Fixed sockets
1	IAC502R	Rotatable sockets
1	IAC532F	2 gang individually fused 3-15 A – fixed sockets
1	IAC532R	3-15 A – rotatable sockets

Pack	Cat. Nos.	Socket modules – low noise / clean earth (green sockets) (continued)
		3 gang unfused
1	IAC503F	Fixed sockets
1	IAC503R	Rotatable sockets
		3 gang individually fused
1	IAC533F	3-15 A – fixed sockets
1	IAC533R	3-15 A – rotatable sockets
		4 gang unfused
1	IAC504F	Fixed sockets
1	IAC504R	Rotatable sockets
		4 gang individually fused
1	IAC534F	3-15 A – fixed sockets
1	IAC534R	3-15 A – rotatable

Pack	Cat. Nos.	End cap
1	IAZ001A	Blank end cap

Pack	Cat. Nos.	Intersoc to Intersoc pre-wired interconnection
		16 A
1	IAB603A	0-3 m length
1	IAB605A	0-5 m length
1	IAB610A	1 m length
1	IAB620A	2 m length
1	IAB630A	3 m length
1	IAB650A	5 m length
		32 A
1	IAB703A	0-3 m length
1	IAB705A	0-5 m length
1	IAB710A	1 m length
1	IAB720A	2 m length
1	IAB730A	3 m length
1	IAB750A	5 m length

Pack	Cat. Nos.	Power out end caps 16 A
		Without flex
1	IAB600B	End cap with female GST connector
1	IAB600C	End cap with female ST connector
		With flex to female GST connector
1	IAB610B	1 m length
1	IAB620B	2 m length
1	IAB630B	3 m length