















## On-desk modules










For other options, e.g. USB A and C, please contact us on +44 (0) 370 608 9020

 					
	Description	Finish	Cat. Nos.	Cat. Nos.	Cat. Nos.
	2 x sockets individually fused at 3·15 A	White	PA3320AA	PB1320AA	PD1320AA
		Black	PA3320AAB <sup>1</sup>	-	PD1320AAB <sup>1</sup>
	3 x sockets individually fused at 3·15 A	White	PA3330AA	PB1330AA	PD1330AA
		Black	PA3330AAB <sup>1</sup>	-	PD1330AAB <sup>1</sup>
	4 x sockets individually fused at 3·15 A	White	PA3340AA	PB1340AA	PD1340AA
		Black	PA3340AAB <sup>1</sup>	-	PD1340AAB <sup>1</sup>
	2 x sockets individually fused at 3·15 A plus 1 x rear pluggable CAT 5e / CAT 6 RJ45 outlet	White	PA3320AB	PB1320AB	PD1320AB
	2 x sockets individually fused at 3·15 A plus 2 x rear pluggable CAT 5e / CAT 6 RJ45 outlets	White	PA3320AC	PB1320AC	PD1320AC
	2 x sockets individually fused at 3·15 A plus 1 x rear pluggable data USB outlet	White	PA3320AD	PB1320AD	PD1320AD
	2 x sockets individually fused at 3·15 A plus 2 x rear pluggable data USB outlets	White	PA3320AE	PB1320AE	PD1320AE
	2 x sockets individually fused at 3·15 A plus 1 x CAT 6A RJ45 outlet with 3 m data lead	White	PA3320AF	PB1320AF	PD1320AF
	2 x sockets individually fused at 3·15 A plus 2 x CAT 6A RJ45 outlets with 3 m data leads	White	PA3320AG	PB1320AG	PD1320AG

Fixings	
Description	Cat. No.
Desk clamp	0546 99

<sup>1</sup> : For the black version add a B to the existing white Cat. No. i.e. white Cat. No. PA3320AA becomes Cat. No. PA3320AAB for black

For other options, e.g. USB A and C, please contact us on +44 (0) 370 608 9020

				Pre-wired with 3 m flex and BS 1363 plug	Pre-wired with 1.5 m flex and GST connector	Pre-wired with 1.5 m flex and Intersoc-R connector
		Description	Finish	Cat. Nos.	Cat. Nos.	Cat. Nos.
		2 x sockets individually fused at 3.15 A plus carrier to accept 1 x Euro Module (25 x 50 mm)	White	PA3320AK	PB1320AK	PD1320AK
		2 x sockets individually fused at 3.15 A plus carrier to accept 2 x Euro Modules (50 x 50 mm)	White	PA3320AL	PB1320AL	PD1320AL
		3 x sockets individually fused at 3.15 A plus 1 x rear pluggable CAT 5e / CAT 6 RJ45 outlet	White	PA3330AB	PB1330AB	PD3330AB
		3 x sockets individually fused at 3.15 A plus 2 x rear pluggable CAT 5e / CAT 6 RJ45 outlets	White	PA3330AC	PB1330AC	PD1330AC
		3 x sockets individually fused at 3.15 A plus 1 x rear pluggable data USB outlet	White	PA3330AD	PB1330AD	PD1330AD
		3 x sockets individually fused at 3.15 A plus 2 x rear pluggable data USB outlets	White	PA3330AE	PB1330AE	PD1330AE
		2G 6A Indian non-switched – 1.5 ISOC and no data	White	–	–	PD1P20AA
		2G 6A Indian non-switched – 1.5 ISOC and 1 x C5/6	White	–	–	PD1P20AB
		2G 6A Indian non-switched – 1.5 ISOC and 2 x C5/6	White	–	–	PD1P20AC

**Notes:**

Other options are available to special order. Contact us on +44 (0) 345 605 4333  
 CAT 5e / CAT 6 outlets have a rear facing RJ45 that will accept either CAT 5e or CAT 6 data cabling (no data cabling is included with the product)  
 CAT 6A outlets are supplied with 3 m pre-wired lead and performance certificate  
 The data USB outlets have a short flying lead at the rear for USB connection to the PC (no additional data cabling is included with the product)  
 Units supplied with carriers to accept Euro Modules will be supplied with apertures at the rear for the passing of data or AV cables