

Electrak® 30 2P + E Buscom trunking

power and communication distribution



CCA3145C



CCA2145C





CCA14RFC





CCA14LFC

 Dimensions and technical information p. 68-73

Integral communication bus suitable for Lonworks, DALI protocols, etc. 25 A and 40 A systems
 IP 4X ingress protection
 Fast installation (trunking push fits together in seconds). High quality materials

Pack	Cat. Nos.	Electrak 30 2P + E with comms									
		2P + E Buscom trunking system with integral communications bus circuit Socket outlets colour coded white									
		Trunking lengths									
		Trunking lengths push fit into each other, and feed units. Trunking lengths can be suspended using the various bracket options									
		<table border="1"> <thead> <tr> <th>Length (m)</th> <th>Tap-off outlets</th> <th>Weight (kg)</th> </tr> </thead> <tbody> <tr> <td>3</td> <td>6</td> <td>4.47</td> </tr> <tr> <td>2</td> <td>4</td> <td>3.27</td> </tr> </tbody> </table>	Length (m)	Tap-off outlets	Weight (kg)	3	6	4.47	2	4	3.27
Length (m)	Tap-off outlets	Weight (kg)									
3	6	4.47									
2	4	3.27									
1	25 A BBA3145C										
1	BBA2145C										
1	40 A CCA3145C										
1	CCA2145C										

Pack	Cat. Nos.	Electrak 30 2 P + E without comms									
		2P + E Busbar (power only) trunking system Socket outlets colour coded white									
		Trunking lengths									
		Trunking lengths push fit into each other, and feed units or flexible lengths. Trunking lengths can be surface mounted suspended using the various bracket options									
		<table border="1"> <thead> <tr> <th>Length (m)</th> <th>Tap-off outlets</th> <th>Weight (kg)</th> </tr> </thead> <tbody> <tr> <td>3</td> <td>6</td> <td>4.47</td> </tr> <tr> <td>2</td> <td>4</td> <td>3.27</td> </tr> </tbody> </table>	Length (m)	Tap-off outlets	Weight (kg)	3	6	4.47	2	4	3.27
Length (m)	Tap-off outlets	Weight (kg)									
3	6	4.47									
2	4	3.27									
1	25 A BBA3145										
1	BBA2145										
1	40 A CCA3145										
1	CCA2145										

Feed units (with comms)			
		Feed units come with 2 x 25 mm Ø and 2 x 16 mm Ø cable entry holes and single screw cable terminals for power and data Left feed units are supplied with right end stop Right feed units are supplied with left end stop	
		Suspended	
			Weight (kg)
1	BBA14LFC	25 A left	1.22
1	BBA14RFC	25 A right	1.49
1	CCA14LFC	40 A left	1.27
1	CCA14RFC	40 A right	1.49

Feed units (without comms – power only)			
		Feed units come with 2 x 25 mm Ø cable entry holes and single screw cable terminals Left feed units are supplied with right end stop Right feed units are supplied with left end stop	
		Suspended	
			Weight (kg)
1	BBA14LF	25 A left	1.22
1	BBA14RF	25 A right	1.49
1	CCA14LF	40 A left	1.27
1	CCA14RF	40 A right	1.49