

HRC blade type cartridge fuses

gG/aM type



Dimensions p. 25

| Pack | Cat. Nos. | Type gG (IEC)/gL (VDE) | | |
|------|----------------------|---|---------------|--------------------------|
| | | HRC (high rupturing capacity) Conform to BS EN 60269-1 and 2, IEC 60269-1, 2 and 2-1, VDE 0636-21 Bureau Veritas approved Fully insulated end plate and handle lugs | | |
| | | With indicator | Rating (Amps) | Voltage ~ (Volts) |
| | | | | Breaking capacity (Amps) |
| | | Size 00 | | |
| 10 | 0163 18 | | 25 | 500 |
| 10 | 0163 20 | | 32 | |
| 10 | 0163 25 | | 40 | |
| 10 | 0163 30 | | 50 | |
| 10 | 0163 35 | | 63 | |
| 10 | 0163 40 | | 80 | |
| 10 | 0163 45 | | 100 | |
| 10 | 0163 50 | | 125 | |
| 10 | 0163 55 | | 160 | |
| | | Size 0 | | |
| 3 | 0168 45 | | 100 | 500 |
| 3 | 0168 50 | | 125 | |
| 3 | 0168 55 | | 160 | |
| 3 | 0168 60 ¹ | | 200 | |
| | | Size 1 | | |
| 3 | 0173 50 | | 125 | 500 |
| 3 | 0173 55 | | 160 | |
| 3 | 0173 60 | | 200 | |
| 3 | 0173 65 | | 250 | |
| | | Size 2 | | |
| 3 | 0178 60 | | 200 | 500 |
| 3 | 0178 65 | | 250 | |
| 3 | 0178 70 | | 315 | |
| 3 | 0178 75 | | 400 | |

| Pack | Cat. Nos. | Type aM (motor rated) | | |
|------|-----------|---|---------------|--------------------------|
| | | HRC (high rupturing capacity) Conform to BS EN 60269-1 and 2, IEC 60269-1, 2 and 2-1, VDE 0636-21 Bureau Veritas approved Fully insulated end plate and handle lugs | | |
| | | With indicator | Rating (Amps) | Voltage ~ (Volts) |
| | | | | Breaking capacity (Amps) |
| | | Size 00 | | |
| 3 | 0160 25 | | 40 | 500 |
| 3 | 0160 30 | | 50 | |
| 3 | 0160 35 | | 63 | |
| 3 | 0160 40 | | 80 | |
| 3 | 0160 45 | | 100 | |
| 3 | 0160 50 | | 125 | |
| | | Size 0 | | |
| 3 | 0165 35 | | 63 | 500 |
| 3 | 0165 40 | | 80 | |
| 3 | 0165 45 | | 100 | |
| 3 | 0165 50 | | 125 | |
| 3 | 0165 55 | | 160 | |
| | | Size 1 | | |
| 3 | 0170 50 | | 125 | 500 |
| 3 | 0170 55 | | 160 | |
| 3 | 0170 60 | | 200 | |
| 3 | 0170 65 | | 250 | |
| | | Size 2 | | |
| 3 | 0175 60 | | 200 | 500 |
| 3 | 0175 65 | | 250 | |
| 3 | 0175 70 | | 315 | |

Neutral blades

| | | |
|---|---------|--------|
| 1 | 0168 04 | Size 0 |
| 1 | 0173 04 | Size 1 |
| 1 | 0178 04 | Size 2 |
| 1 | 0181 04 | Size 3 |

Handle

| | | |
|---|---------|--------------------------------|
| 5 | 0199 02 | Removable handle for all sizes |
|---|---------|--------------------------------|

1 : Overrating not described by standards