

CX³ power contactors with handle

16 A to 63 A



4125 44



4125 56



4124 29



4124 31

Technical information p. 44
Dimensions p. 47

Conform to IEC/EN 61095
Space for power supply busbar on top (up to 25 A)

Pack	Cat. Nos.	Power contactors with 230 V~ coil and handle			
		Manual override for test and repair function, carried out via the handle Permanent "ON" or "OFF" without automatic reset			
		Double pole - 250 V~			
4	4125 44	I max	Connection	Type of contact	Number of modules
1	4125 45 ¹	25 A		2 N/O	1
1	4125 47 ¹	40 A		2 N/O	2
1	4125 47 ¹	63 A		2 N/O	2
		Triple pole 400 V~			
1	4125 49 ¹	40 A		3 N/O	3
1	4125 50 ¹	63 A		3 N/O	3
		Four pole 400 V~			
1	4125 53 ¹	40 A		4 N/O	3
1	4125 56 ¹	63 A		4 N/O	3

Pack	Cat. Nos.	Signalling auxiliaries for CX ³ contactors			
		Auxiliary changeover switch Used to signal the position status of the contacts on the product to which it is connected			
		For 1 module contactors 16 A to 25 A Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4124 29	I max	Voltage	Contact	Number of modules
		5 A	250 V~	N/C + N/O	0-5
		For 2 module contactors 25 A Maximum 2 auxiliary devices per contactor Fitted on left-hand side of contactor			
1	4124 30	5 A	250 V~	N/C + N/O	0-5
		For 40 and 63 A contactors Maximum 1 auxiliary device per contactor Fitted on left-hand side of contactor			
1	4124 31	5 A	250 V~	N/C + N/O	0-5
		Accessory			
10	4063 07	Spacing unit 0.5 module To be placed between every 2 contactors to aid cooling			



1 : Handle can be accessed after removing blanking plate