

# Salamandre® distribution trunking

standard and IP4X trunking ranges

## STANDARD TRUNKING RANGE

TRUNKING		FITTINGS										
Size (mm)	Lengths, lids and couplers	Top lid 90° bends – gussett	Top lid 90° bends – square	Inside lid 90° bends – gussett	Inside lid 90° bends – square	Outside lid 90° bends – gussett	Outside lid 90° bends – square	Top lid 45° bends	Inside lid 45° bends	Outside lid 45° bends	Top lid tees – gussett	Top lid tees – square
50 x 50	MGR22	MGR22AGL	MGR22ASL	MGR22BGL	MGR22BSL	MGR22CGL	MGR22CSL	MGR22AL	MGR22BL	MGR22CL	MGR22AGT	MGR22AST
75 x 50	MGR32	MGR32AGL	MGR32ASL	MGR32BGL	MGR32BSL	MGR32CGL	MGR32CSL	MGR32AL	MGR32BL	MGR32CL	MGR32AGT	MGR32AST
75 x 75	MGR33	MGR33AGL	MGR33ASL	MGR33BGL	MGR33BSL	MGR33CGL	MGR33CSL	MGR33AL	MGR33BL	MGR33CL	MGR33AGT	MGR33AST
100 x 50	MGR42	MGR42AGL	MGR42ASL	MGR42BGL	MGR42BSL	MGR42CGL	MGR42CSL	MGR42AL	MGR42BL	MGR42CL	MGR42AGT	MGR42AST
100 x 75	MGR43	MGR43AGL	MGR43ASL	MGR43BGL	MGR43BSL	MGR43CGL	MGR43CSL	MGR43AL	MGR43BL	MGR43CL	MGR43AGT	MGR43AST
100 x 100	MGR44	MGR44AGL	MGR44ASL	MGR44BGL	MGR44BSL	MGR44CGL	MGR44CSL	MGR44AL	MGR44BL	MGR44CL	MGR44AGT	MGR44AST
150 x 50	MGR62	MGR62AGL	MGR62ASL	MGR62BGL	MGR62BSL	MGR62CGL	MGR62CSL	MGR62AL	MGR62BL	MGR62CL	MGR62AGT	MGR62AST
150 x 75	MGR63	MGR63AGL	MGR63ASL	MGR63BGL	MGR63BSL	MGR63CGL	MGR63CSL	MGR63AL	MGR63BL	MGR63CL	MGR63AGT	MGR63AST
150 x 100	MGR64	MGR64AGL	MGR64ASL	MGR64BGL	MGR64BSL	MGR64CGL	MGR64CSL	MGR64AL	MGR64BL	MGR64CL	MGR64AGT	MGR64AST
150 x 150	MGR66	MGR66AGL	MGR66ASL	MGR66BGL	MGR66BSL	MGR66CGL	MGR66CSL	MGR66AL	MGR66BL	MGR66CL	MGR66AGT	MGR66AST
225 x 75	MGR93	MGR93AGL	MGR93ASL	MGR93BGL	MGR93BSL	MGR93CGL	MGR93CSL	MGR93AL	MGR93BL	MGR93CL	MGR93AGT	MGR93AST
225 x 100	MGR94	MGR94AGL	MGR94ASL	MGR94BGL	MGR94BSL	MGR94CGL	MGR94CSL	MGR94AL	MGR94BL	MGR94CL	MGR94AGT	MGR94AST
225 x 150	MGR96	MGR96AGL	MGR96ASL	MGR96BGL	MGR96BSL	MGR96CGL	MGR96CSL	MGR96AL	MGR96BL	MGR96CL	MGR96AGT	MGR96AST
225 x 225	MGR99	MGR99AGL	MGR99ASL	MGR99BGL	MGR99BSL	MGR99CGL	MGR99CSL	MGR99AL	MGR99BL	MGR99CL	MGR99AGT	MGR99AST
300 x 75	MGR123	MGR123AGL	MGR123ASL	MGR123BGL	MGR123BSL	MGR123CGL	MGR123CSL	MGR123AL	MGR123BL	MGR123CL	MGR123AGT	MGR123AST
300 x 100	MGR124	MGR124AGL	MGR124ASL	MGR124BGL	MGR124BSL	MGR124CGL	MGR124CSL	MGR124AL	MGR124BL	MGR124CL	MGR124AGT	MGR124AST
300 x 150	MGR126	MGR126AGL	MGR126ASL	MGR126BGL	MGR126BSL	MGR126CGL	MGR126CSL	MGR126AL	MGR126BL	MGR126CL	MGR126AGT	MGR126AST
300 x 300	MGR1212	MGR1212AGL	MGR1212ASL	MGR1212BGL	MGR1212BSL	MGR1212CGL	MGR1212CSL	MGR1212AL	MGR1212BL	MGR1212CL	MGR1212AGT	MGR1212AST

## IP4X TRUNKING RANGE

TRUNKING		FITTINGS								
Size (mm)	Lengths, lids and couplers	Cover strap IP4X	Top lid 90° bends – gussett IP4X	Top lid 90° bends – square IP4X	Inside lid 90° bends – gussett IP4X	Inside lid 90° bends – square IP4X	Outside lid 90° bends – gussett IP4X	Outside lid 90° bends – square IP4X	Top lid 45° bends IP4X	Inside lid 45° bends IP4X
50 x 50	MGR22	MGIP2CS	MGIP22AGL	MGIP22ASL	MGIP22BGL	MGIP22BSL	MGIP22CGL	MGIP22CSL	MGIP22AL	MGIP22BL
75 x 50	MGR32	MGIP3CS	MGIP32AGL	MGIP32ASL	MGIP32BGL	MGIP32BSL	MGIP32CGL	MGIP32CSL	MGIP32AL	MGIP32BL
75 x 75	MGR33	MGIP3CS	MGIP33AGL	MGIP33ASL	MGIP33BGL	MGIP33BSL	MGIP33CGL	MGIP33CSL	MGIP33AL	MGIP33BL
100 x 50	MGR42	MGIP4CS	MGIP42AGL	MGIP42ASL	MGIP42BGL	MGIP42BSL	MGIP42CGL	MGIP42CSL	MGIP42AL	MGIP42BL
100 x 75	MGR43	MGIP4CS	MGIP43AGL	MGIP43ASL	MGIP43BGL	MGIP43BSL	MGIP43CGL	MGIP43CSL	MGIP43AL	MGIP43BL
100 x 100	MGR44	MGIP4CS	MGIP44AGL	MGIP44ASL	MGIP44BGL	MGIP44BSL	MGIP44CGL	MGIP44CSL	MGIP44AL	MGIP44BL
150 x 50	MGR62	MGIP6CS	MGIP62AGL	MGIP62ASL	MGIP62BGL	MGIP62BSL	MGIP62CGL	MGIP62CSL	MGIP62AL	MGIP62BL
150 x 75	MGR63	MGIP6CS	MGIP63AGL	MGIP63ASL	MGIP63BGL	MGIP63BSL	MGIP63CGL	MGIP63CSL	MGIP63AL	MGIP63BL
150 x 100	MGR64	MGIP6CS	MGIP64AGL	MGIP64ASL	MGIP64BGL	MGIP64BSL	MGIP64CGL	MGIP64CSL	MGIP64AL	MGIP64BL
150 x 150	MGR66	MGIP6CS	MGIP66AGL	MGIP66ASL	MGIP66BGL	MGIP66BSL	MGIP66CGL	MGIP66CSL	MGIP66AL	MGIP66BL
225 x 75	MGR93	MGIP9CS	MGIP93AGL	MGIP93ASL	MGIP93BGL	MGIP93BSL	MGIP93CGL	MGIP93CSL	MGIP93AL	MGIP93BL
225 x 100	MGR94	MGIP9CS	MGIP94AGL	MGIP94ASL	MGIP94BGL	MGIP94BSL	MGIP94CGL	MGIP94CSL	MGIP94AL	MGIP94BL
225 x 150	MGR96	MGIP9CS	MGIP96AGL	MGIP96ASL	MGIP96BGL	MGIP96BSL	MGIP96CGL	MGIP96CSL	MGIP96AL	MGIP96BL
225 x 225	MGR99	MGIP9CS	MGIP99AGL	MGIP99ASL	MGIP99BGL	MGIP99BSL	MGIP99CGL	MGIP99CSL	MGIP99AL	MGIP99BL
300 x 75	MGR123	MGIP12CS	MGIP123AGL	MGIP123ASL	MGIP123BGL	MGIP123BSL	MGIP123CGL	MGIP123CSL	MGIP123AL	MGIP123BL
300 x 100	MGR124	MGIP12CS	MGIP124AGL	MGIP124ASL	MGIP124BGL	MGIP124BSL	MGIP124CGL	MGIP124CSL	MGIP124AL	MGIP124BL
300 x 150	MGR126	MGIP12CS	MGIP126AGL	MGIP126ASL	MGIP126BGL	MGIP126BSL	MGIP126CGL	MGIP126CSL	MGIP126AL	MGIP126BL
300 x 300	MGR1212	MGIP12CS	MGIP1212AGL	MGIP1212ASL	MGIP1212BGL	MGIP1212BSL	MGIP1212CGL	MGIP1212CSL	MGIP1212AL	MGIP1212BL

### STANDARD TRUNKING RANGE

FITTINGS										ACCESSORIES				
Inside lid tees – gusset	Outside lid tees – gusset	Offset tees <sup>(1)</sup>	Cross-overs	Offset cross-overs <sup>(1)</sup>	Reducers <sup>(2)</sup>	Bell-mouths	Change faces – left hand <sup>(3)</sup>	Change faces – right hand <sup>(3)</sup>	Pin racks	End caps	Flanges	Fitting to fitting adaptors	Trunking couplers	
MGR22BGT	MGR22CGT	MGR22OST2C	MGR22AGX	MGR22OSX2C	–	MGR22B	MSIP22CLH	MSIP22CRH	MGR22PR	MGR22E	MGR22F	MGR22FA	MGR22C	
MGR32BGT	MGR32CGT	MGR32OST2C	MGR32AGX	MGR32OSX2C	MGR32 Z R	MGR32B	–	–	MGR32PR	MGR32E	MGR32F	MGR32FA	MGR32C	
MGR33BGT	MGR33CGT	MGR33OST2C	MGR33AGX	MGR33OSX2C	MGR33 Z R	MGR33B	MSIP33CLH	MSIP33CRH	MGR33PR	MGR33E	MGR33F	MGR33FA	MGR33C	
MGR42BGT	MGR42CGT	MGR42OST2C	MGR42AGX	MGR42OSX2C	MGR42 Z R	MGR42B	–	–	MGR42PR	MGR42E	MGR42F	MGR42FA	MGR42C	
MGR43BGT	MGR43CGT	MGR43OST2C	MGR43AGX	MGR43OSX2C	MGR43 Z R	MGR43B	–	–	MGR43PR	MGR43E	MGR43F	MGR43FA	MGR43C	
MGR44BGT	MGR44CGT	MGR44OST2C	MGR44AGX	MGR44OSX2C	MGR44 Z R	MGR44B	MSIP44CLH	MSIP44CRH	MGR44PR	MGR44E	MGR44F	MGR44FA	MGR44C	
MGR62BGT	MGR62CGT	MGR62OST2C	MGR62AGX	MGR62OSX2C	MGR62 Z R	MGR62B	–	–	MGR62PR	MGR62E	MGR62F	MGR62FA	MGR62C	
MGR63BGT	MGR63CGT	MGR63OST2C	MGR63AGX	MGR63OSX2C	MGR63 Z R	MGR63B	–	–	MGR63PR	MGR63E	MGR63F	MGR63FA	MGR63C	
MGR64BGT	MGR64CGT	MGR64OST2C	MGR64AGX	MGR64OSX2C	MGR64 Z R	MGR64B	–	–	MGR64PR	MGR64E	MGR64F	MGR64FA	MGR64C	
MGR66BGT	MGR66CGT	MGR66OST2C	MGR66AGX	MGR66OSX2C	MGR66 Z R	MGR66B	MSIP66CLH	MSIP66CRH	MGR66PR	MGR66E	MGR66F	MGR66FA	MGR66C	
MGR93BGT	MGR93CGT	MGR93OST2C	MGR93AGX	MGR93OSX2C	MGR93 Z R	MGR93B	–	–	MGR93PR	MGR93E	MGR93F	MGR93FA	MGR93C	
MGR94BGT	MGR94CGT	MGR94OST2C	MGR94AGX	MGR94OSX2C	MGR94 Z R	MGR94B	–	–	MGR94PR	MGR94E	MGR94F	MGR94FA	MGR94C	
MGR96BGT	MGR96CGT	MGR96OST2C	MGR96AGX	MGR96OSX2C	MGR96 Z R	MGR96B	–	–	MGR96PR	MGR96E	MGR96F	MGR96FA	MGR96C	
MGR99BGT	MGR99CGT	MGR99OST2C	MGR99AGX	MGR99OSX2C	MGR99 Z R	MGR99B	MSIP99CLH	MSIP99CRH	MGR99PR	MGR99E	MGR99F	MGR99FA	MGR99C	
MGR123BGT	MGR123CGT	MGR123OST2C	MGR123AGX	MGR123OSX2C	MGR123 Z R	MGR123B	–	–	MGR123PR	MGR123E	MGR123F	MGR123FA	MGR123C	
MGR124BGT	MGR124CGT	MGR124OST2C	MGR124AGX	MGR124OSX2C	MGR124 Z R	MGR124B	–	–	MGR124PR	MGR124E	MGR124F	MGR124FA	MGR124C	
MGR126BGT	MGR126CGT	MGR126OST2C	MGR126AGX	MGR126OSX2C	MGR126 Z R	MGR126B	–	–	MGR126PR	MGR126E	MGR126F	MGR126FA	MGR126C	
MGR1212BGT	MGR1212CGT	MGR1212OST2C	MGR1212AGX	MGR1212OSX2C	MGR1212 Z R	MGR1212B	MSIP1212CLH	MSIP1212CRH	MGR1212PR	MGR1212E	MGR1212F	MGR1212FA	MGR1212C	

(1) Not available in single compartment. Cat. Nos. shown are for 2 compartment option. For 3 compartment option, replace 2C with 3C  
 (2) Replace Z with reduced trunking size code required (see p. 10) (3) For non square sizes refer to instructions on p. 25

### IP4X TRUNKING RANGE

FITTINGS										ACCESSORIES			
Outside lid 45° bends IP4X	Top lid tees – gusset IP4X	Top lid tees – square IP4X	Inside lid tees – gusset IP4X	Outside lid tees – gusset IP4X	Cross-overs IP4X	Reducers <sup>(1)</sup> IP4X	Bellmouths IP4X	Change faces – left hand <sup>(2)</sup>	Change faces – right hand <sup>(2)</sup>	End caps IP4X	Flanges IP4X	Trunking couplers	
MGIP22CL	MGIP22AGT	MGIP22AST	MGIP22BGT	MGIP22CGT	MGIP22AGX	–	MGIP22B	MSIP22CLH	MSIP22CRH	MGIP22E	MGIP22F	MGR22C	
MGIP32CL	MGIP32AGT	MGIP32AST	MGIP32BGT	MGIP32CGT	MGIP32AGX	MGIP32 Z R	MGIP32B	–	–	MGIP32E	MGIP32F	MGR32C	
MGIP33CL	MGIP33AGT	MGIP33AST	MGIP33BGT	MGIP33CGT	MGIP33AGX	MGIP33 Z R	MGIP33B	MSIP33CLH	MSIP33CRH	MGIP33E	MGIP33F	MGR33C	
MGIP42CL	MGIP42AGT	MGIP42AST	MGIP42BGT	MGIP42CGT	MGIP42AGX	MGIP42 Z R	MGIP42B	–	–	MGIP42E	MGIP42F	MGR42C	
MGIP43CL	MGIP43AGT	MGIP43AST	MGIP43BGT	MGIP43CGT	MGIP43AGX	MGIP43 Z R	MGIP43B	–	–	MGIP43E	MGIP43F	MGR43C	
MGIP44CL	MGIP44AGT	MGIP44AST	MGIP44BGT	MGIP44CGT	MGIP44AGX	MGIP44 Z R	MGIP44B	MSIP44CLH	MSIP44CRH	MGIP44E	MGIP44F	MGR44C	
MGIP62CL	MGIP62AGT	MGIP62AST	MGIP62BGT	MGIP62CGT	MGIP62AGX	MGIP62 Z R	MGIP62B	–	–	MGIP62E	MGIP62F	MGR62C	
MGIP63CL	MGIP63AGT	MGIP63AST	MGIP63BGT	MGIP63CGT	MGIP63AGX	MGIP63 Z R	MGIP63B	–	–	MGIP63E	MGIP63F	MGR63C	
MGIP64CL	MGIP64AGT	MGIP64AST	MGIP64BGT	MGIP64CGT	MGIP64AGX	MGIP64 Z R	MGIP64B	–	–	MGIP64E	MGIP64F	MGR64C	
MGIP66CL	MGIP66AGT	MGIP66AST	MGIP66BGT	MGIP66CGT	MGIP66AGX	MGIP66 Z R	MGIP66B	MSIP66CLH	MSIP66CRH	MGIP66E	MGIP66F	MGR66C	
MGIP93CL	MGIP93AGT	MGIP93AST	MGIP93BGT	MGIP93CGT	MGIP93AGX	MGIP93 Z R	MGIP93B	–	–	MGIP93E	MGIP93F	MGR93C	
MGIP94CL	MGIP94AGT	MGIP94AST	MGIP94BGT	MGIP94CGT	MGIP94AGX	MGIP94 Z R	MGIP94B	–	–	MGIP94E	MGIP94F	MGR94C	
MGIP96CL	MGIP96AGT	MGIP96AST	MGIP96BGT	MGIP96CGT	MGIP96AGX	MGIP96 Z R	MGIP96B	–	–	MGIP96E	MGIP96F	MGR96C	
MGIP99CL	MGIP99AGT	MGIP99AST	MGIP99BGT	MGIP99CGT	MGIP99AGX	MGIP99 Z R	MGIP99B	MSIP99CLH	MSIP99CRH	MGIP99E	MGIP99F	MGR99C	
MGIP123CL	MGIP123AGT	MGIP123AST	MGIP123BGT	MGIP123CGT	MGIP123AGX	MGIP123 Z R	MGIP123B	–	–	MGIP123E	MGIP123F	MGR123C	
MGIP124CL	MGIP124AGT	MGIP124AST	MGIP124BGT	MGIP124CGT	MGIP124AGX	MGIP124 Z R	MGIP124B	–	–	MGIP124E	MGIP124F	MGR124C	
MGIP126CL	MGIP126AGT	MGIP126AST	MGIP126BGT	MGIP126CGT	MGIP126AGX	MGIP126 Z R	MGIP126B	–	–	MGIP126E	MGIP126F	MGR126C	
MGIP1212CL	MGIP1212AGT	MGIP1212AST	MGIP1212BGT	MGIP1212CGT	MGIP1212AGX	MGIP1212 Z R	MGIP1212B	MSIP1212CLH	MSIP1212CRH	MGIP1212E	MGIP1212F	MGR1212C	

(1) Replace Z with reduced trunking size code required (see p. 10)  
 (2) For non square sizes refer to instructions on p. 27