

Salamandre® lighting trunking

selection chart

LIGHTING TRUNKING RANGE

TRUNKING		FITTINGS										
Finish	Size (mm)	Lengths	Galvanised lid	White plastic standard lids	Top lid 90° bends	Inside lid 90° bends	Outside lid 90° bends	Top lid 45° bends	Inside lid 45° bends	Outside lid 45° bends	Top lid tees	
Galvanised	50 x 50	LT2	LT2GC	LT2PC	LT2ASL	LT2BSL	LT2CSL	LT2AL	LT2BL	LT2CL	LT2AST	
Powder coated	50 x 50	WLT2	WLT2GC	LT2PC	WLT2ASL	WLT2BSL	WLT2CSL	WLT2AL	WLT2BL	WLT2CL	WLT2AST	
FITTINGS				ACCESSORIES								
Finish	Inside lid tees	Outside lid tees	Crossovers	End caps	Flanges	Girder clamps	Stirrup hangers	Suspension units	Pull switch adaptors	Cable retainers	Klik adaptors	Long couplers
Galvanised	LT2BST	LT2CST	LT2ASX	LT2E	LT2F	LT2GCL	LT2H	LT2FS	LT2PSA	LT2CR	LT2KL	LT2C
Powder coated	WLT2BST	WLT2CST	WLT2ASX	WLT2E	WLT2F	WLT2GCL	WLT2H	LT2FS	LT2PSA	LT2CR	LT2KL	LT2C