

Salamandre® IP55 rated trunking

IP55 rated trunking range

| TRUNKING | | | FITTINGS | | | | | | | |
|----------------------|---------|-----------|----------------------------|----------------------------|-------------------------------|-------------------------------|--------------------------------|--------------------------------|-------------------|--|
| Size (mm) | Lengths | Lids | Top lid 90° bends – gusset | Top lid 90° bends – square | Inside lid 90° bends – gusset | Inside lid 90° bends – square | Outside lid 90° bends – gusset | Outside lid 90° bends – square | Top lid 45° bends | |
| 1 COMPARTMENT | | | | | | | | | | |
| 50 x 50 | WSTIP22 | WSTIP2LID | WSTIP22AGL | WSTIP22ASL | WSTIP22BGL | WSTIP22BSL | WSTIP22CGL | WSTIP22CSL | WSTIP22AL | |
| 75 x 50 | WSTIP32 | WSTIP3LID | WSTIP32AGL | WSTIP32ASL | WSTIP32BGL | WSTIP32BSL | WSTIP32CGL | WSTIP32CSL | WSTIP32AL | |
| 100 x 50 | WSTIP42 | WSTIP4LID | WSTIP42AGL | WSTIP42ASL | WSTIP42BGL | WSTIP42BSL | WSTIP42CGL | WSTIP42CSL | WSTIP42AL | |
| 100 x 75 | WSTIP43 | WSTIP4LID | WSTIP43AGL | WSTIP43ASL | WSTIP43BGL | WSTIP43BSL | WSTIP43CGL | WSTIP43CSL | WSTIP43AL | |
| 100 x 100 | WSTIP44 | WSTIP4LID | WSTIP44AGL | WSTIP44ASL | WSTIP44BGL | WSTIP44BSL | WSTIP44CGL | WSTIP44CSL | WSTIP44AL | |
| 150 x 50 | WSTIP62 | WSTIP6LID | WSTIP62AGL | WSTIP62ASL | WSTIP62BGL | WSTIP62BSL | WSTIP62CGL | WSTIP62CSL | WSTIP62AL | |
| 150 x 75 | WSTIP63 | WSTIP6LID | WSTIP63AGL | WSTIP63ASL | WSTIP63BGL | WSTIP63BSL | WSTIP63CGL | WSTIP63CSL | WSTIP63AL | |
| 150 x 100 | WSTIP64 | WSTIP6LID | WSTIP64AGL | WSTIP64ASL | WSTIP64BGL | WSTIP64BSL | WSTIP64CGL | WSTIP64CSL | WSTIP64AL | |
| 150 x 150 | WSTIP66 | WSTIP6LID | WSTIP66AGL | WSTIP66ASL | WSTIP66BGL | WSTIP66BSL | WSTIP66CGL | WSTIP66CSL | WSTIP66AL | |
| 225 x 50 | WSTIP92 | WSTIP9LID | WSTIP92AGL | WSTIP92ASL | WSTIP92BGL | WSTIP92BSL | WSTIP92CGL | WSTIP92CSL | WSTIP92AL | |
| 225 x 75 | WSTIP93 | WSTIP9LID | WSTIP93AGL | WSTIP93ASL | WSTIP93BGL | WSTIP93BSL | WSTIP93CGL | WSTIP93CSL | WSTIP93AL | |
| 225 x 100 | WSTIP94 | WSTIP9LID | WSTIP94AGL | WSTIP94ASL | WSTIP94BGL | WSTIP94BSL | WSTIP94CGL | WSTIP94CSL | WSTIP94AL | |
| 225 x 150 | WSTIP96 | WSTIP9LID | WSTIP96AGL | WSTIP96ASL | WSTIP96BGL | WSTIP96BSL | WSTIP96CGL | WSTIP96CSL | WSTIP96AL | |
| 225 x 225 | WSTIP99 | WSTIP9LID | WSTIP99AGL | WSTIP99ASL | WSTIP99BGL | WSTIP99BSL | WSTIP99CGL | WSTIP99CSL | WSTIP99AL | |

Trunking lengths and lids are sold separately

Each trunking length is supplied with one coupler and required TORX®¹ head fixings and earth links

For all 2 compartment Cat. Nos. include 2C at the end of each product code shown above (except lids)

For all 3 compartment Cat. Nos. include 3C at the end of each product code shown above (except lids)

For 3 compartment products sizes 50 x 50 mm and 75 x 50 mm are not available

For all 2 and 3 compartment AGT (top lid tees – gusset), type A or type B cable exit configuration must be specified at time of order, (see p. 16)

1 : TORX® is a registered trademark of Acument Intellectual Properties LLC

| FITTINGS | | | | | | ACCESSORIES | | | | |
|-------------------------|--------------------------|--------------------------|--------------------------------|---------------------------------|------------|-------------|----------|----------|----------------------|--|
| Inside lid 45° bends | Outside lid 45° bends | Top lid tees - gusset | Inside lid tees - gusset | Outside lid tees - gusset | Crossovers | Reducers | End caps | Flanges | Trunking couplers | |
| | | | | | | | | | | |
| WSTIP22BL | WSTIP22CL | WSTIP22AGT | WSTIP22BGT | WSTIP22CGT | WSTIP22AGX | – | WSTIP22E | WSTIP22F | WSTIP22C | |
| WSTIP32BL | WSTIP32CL | WSTIP32AGT | WSTIP32BGT | WSTIP32CGT | WSTIP32AGX | WSTIP32 Z R | WSTIP32E | WSTIP32F | WSTIP32C | |
| WSTIP42BL | WSTIP42CL | WSTIP42AGT | WSTIP42BGT | WSTIP42CGT | WSTIP42AGX | WSTIP42 Z R | WSTIP42E | WSTIP42F | WSTIP42C | |
| WSTIP43BL | WSTIP43CL | WSTIP43AGT | WSTIP43BGT | WSTIP43CGT | WSTIP43AGX | WSTIP43 Z R | WSTIP43E | WSTIP43F | WSTIP43C | |
| WSTIP44BL | WSTIP44CL | WSTIP44AGT | WSTIP44BGT | WSTIP44CGT | WSTIP44AGX | WSTIP44 Z R | WSTIP44E | WSTIP44F | WSTIP44C | |
| WSTIP62BL | WSTIP62CL | WSTIP62AGT | WSTIP62BGT | WSTIP62CGT | WSTIP62AGX | WSTIP62 Z R | WSTIP62E | WSTIP62F | WSTIP62C | |
| WSTIP63BL | WSTIP63CL | WSTIP63AGT | WSTIP63BGT | WSTIP63CGT | WSTIP63AGX | WSTIP63 Z R | WSTIP63E | WSTIP63F | WSTIP63C | |
| WSTIP64BL | WSTIP64CL | WSTIP64AGT | WSTIP64BGT | WSTIP64CGT | WSTIP64AGX | WSTIP64 Z R | WSTIP64E | WSTIP64F | WSTIP64C | |
| WSTIP66BL | WSTIP66CL | WSTIP66AGT | WSTIP66BGT | WSTIP66CGT | WSTIP66AGX | WSTIP66 Z R | WSTIP66E | WSTIP66F | WSTIP66C | |
| WSTIP92BL | WSTIP92CL | WSTIP92AGT | WSTIP92BGT | WSTIP92CGT | WSTIP92AGX | WSTIP92 Z R | WSTIP92E | WSTIP92F | WSTIP92C | |
| WSTIP93BL | WSTIP93CL | WSTIP93AGT | WSTIP93BGT | WSTIP93CGT | WSTIP93AGX | WSTIP93 Z R | WSTIP93E | WSTIP93F | WSTIP93C | |
| WSTIP94BL | WSTIP94CL | WSTIP94AGT | WSTIP94BGT | WSTIP94CGT | WSTIP94AGX | WSTIP94 Z R | WSTIP94E | WSTIP94F | WSTIP94C | |
| WSTIP96BL | WSTIP96CL | WSTIP96AGT | WSTIP96BGT | WSTIP96CGT | WSTIP96AGX | WSTIP96 Z R | WSTIP96E | WSTIP96F | WSTIP96C | |
| WSTIP99BL | WSTIP99CL | WSTIP99AGT | WSTIP99BGT | WSTIP99CGT | WSTIP99AGX | WSTIP99 Z R | WSTIP99E | WSTIP99F | WSTIP99C | |

Key : Z = trunking size code
 Replace Z with the relevant code (see p. 6)