


Swifts® cable ladder fasteners

medium duty (Topaz), heavy duty (Sapphire) and extra heavy duty (Emerald)



Pack	Cat. Nos.	Fastener sets	
50 50	LFGM10P50 LFSM10P50	Comprise M10 coach bolt and flange nut Hot dip galvanised Stainless steel	
Fasteners			
Hexagon head setscrews			
Electroplated zinc			
200	SS0616	M6 x 16	
200	SS0620	M6 x 20	
200	SS0625	M6 x 25	
200	SS0630	M6 x 30	
200	SS1016	M10 x 16	
200	SS1020	M10 x 20	
200	SS1025	M10 x 25	
200	SS1030	M10 x 30	
100	SS1035	M10 x 35	
100	SS1040	M10 x 40	
100	SS1045	M10 x 45	
100	SS1050	M10 x 50	
100	SS1060	M10 x 60	
100	SS1220	M12 x 20	
100	SS1225	M12 x 25	
100	SS1230	M12 x 30	
100	SS1235	M12 x 35	
100	SS1240	M12 x 40	
100	SS1250	M12 x 50	
Hot dip galvanised			
200	SSG0616	M6 x 16	
200	SSG0620	M6 x 20	
200	SSG0625	M6 x 25	
200	SSG0630	M6 x 30	
Flat washers			
Electroplated zinc			
500	FW06	M6	
500	FW08	M8	
500	FW10	M10	
500	FW12	M12	
Shakeproof washers			
Electroplated zinc			
400	SW06	M6	
400	SW08	M8	
400	SW10	M10	
400	SW12	M12	

Pack	Cat. Nos.	Fasteners (continued)	
Hexagon nuts			
Electroplated zinc			
500	HN06	M6	
500	HN08	M8	
500	HN10	M10	
500	HN12	M12	
Roofing nuts and bolts			
Electroplated zinc			
200	RB0612	M6 x 12	
200	RB0616	M6 x 16	
200	RB0620	M6 x 20	
200	RB0625	M6 x 25	
100	RB0630	M6 x 30	
100	RB0640	M6 x 40	
100	RB0650	M6 x 50	
Hot dip galvanised			
100	RBG0612	M6 x 12	
100	RBG0616	M6 x 16	
Stainless steel			
100	RB0612S	M6 x 12	
100	RB0616S	M6 x 16	
100	RB0620S	M6 x 20	
Threaded rods			
Electroplated zinc			
1	TR06	M6 x 3 m	
1	TR08	M8 x 3 m	
1	TR10	M10 x 3 m	
1	TR12	M12 x 3 m	
Threaded rod connectors			
Electroplated zinc			
1	RC06	M6	
1	RC08	M8	
1	RC10	M10	
1	RC12	M12	