


 Surround plate selection charts **p. 32-35**

 Mechanisms supplied with rocker plates, to be equipped with surround plates (p. 32-35)
 Support frame not needed

Pack	Cat. Nos.	Single pole socket outlets 13 A - 250 V~
10	5721 43	Shuttered for child safety ASTA licence Conform to BS 1363 : Part 2 2P + E switched - 1 gang ○ White ● Magnesium ● Champagne ● Soft Alu
10	5726 43	
10 N	5700 48	
10 N	5710 48	
10	5721 44	2P + E switched + LED - 1 gang ○ White ● Magnesium ● Champagne ● Soft Alu
10	5726 44	
10 N	5724 45	
10 N	5724 44	
5	5721 45	2P + E switched - 2 gang ○ White ● Magnesium ● Champagne ● Soft Alu
5	5726 45	
5 N	5700 49	
5 N	5710 49	
5	5721 46	2P + E switched + LED - 2 gang ○ White ● Magnesium ● Champagne ● Soft Alu
5	5726 46	
5 N	5724 47	
5 N	5724 46	

Pack	Cat. Nos.	Double pole socket outlets 13 A - 250 V~
5	5721 47	Shuttered for child safety ASTA licence Conform to BS 1363 : Part 2 2P + E switched - 1 gang ○ White ● Magnesium ● Champagne ● Soft Alu
5	5726 47	
5 N	5724 49	
5 N	5724 48	
5	5721 49	2P + E switched - 2 gang ○ White ● Magnesium ● Champagne ● Soft Alu ● Red for standard and clean earth applications Non standard pin configuration
5	5726 49	
5 N	5710 70	
5 N	5700 70	
5	5721 41	

Pack	Cat. Nos.	Double pole socket outlets 5 A - 250 V~
10	5721 40	Shuttered for child safety Conform to BS 546 2P + E switched - 1 gang ○ White ● Magnesium ● Champagne ● Soft Alu
10	5726 40	
10 N	5727 58	
10 N	5727 21	

Pack	Cat. Nos.	Fused connection units
		Double pole fused 13 A (fuse supplied) Flex outlet knockout and cord grip Captive fuse carrier (padlockable) Captive terminal screws Conform to BS 1363 : Part 4
		Switched ○ White ● Magnesium ● Champagne ● Soft Alu
5	5721 50	
5	5726 50	
5 N	5726 75	
5 N	5726 74	
		Switched + LED ○ White ● Magnesium ● Champagne ● Soft Alu
5	5721 51	
5	5726 51	
5 N	5726 77	
5 N	5726 76	
		Unswitched ○ White ● Magnesium ● Champagne ● Soft Alu
10	5721 57	
10	5726 57	
10 N	5726 79	
10 N	5726 78	

Pack	Cat. Nos.	Switched USB sockets
		Conform to BS 1363-2 USB chargers conform to BS EN 60950-1
		1 gang switched - single pole USB Type-A 2.4 A - 5 V= - 12 W Consumption in passive mode < 0.08 W
1	5721 56	
1	5726 56	
1 N	5710 80	
1 N	5700 80	
		2 gang switched - single pole USB Type-A + Type-C 3 A - 5 V= - 15 W Consumption in passive mode < 0.08 W
1	5721 42	
1	5726 42	
1 N	5710 81	
1 N	5700 81	