

# Arteor™

## RJ 45 sockets



Support frames and surround plates selection charts **p. 30, 32-35**

With LCS<sup>3</sup> connector with fast connection thanks to integrated crimping  
 Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables  
 Contacts marked with dual colour code and wiring schemes T568A and T568B  
 Conform to standards ISO/IEC 11801 Ed. 2-0, amendment 2, BS EN 50173-1 and TIA/EIA 568 C  
 Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Cat. 6 <sub>A</sub> sockets
		360° metal shielding
		<b>STP</b> 1 module
10	5723 06	○ White
10	5728 06	● Magnesium
10	5728 46	● Champagne
10	5728 45	● Soft Alu
10	5723 51	○ White with orange shutter
10	5728 51	● Magnesium with orange shutter
10	5728 48	● Champagne with orange shutter
10	5728 47	● Soft Alu with orange shutter
10	5723 52	○ White with green shutter
10	5728 52	● Magnesium with green shutter
10	5728 61	● Champagne with green shutter
10	5728 60	● Soft Alu with green shutter
		<b>STP with controlled access</b> 2 modules Supplied with 2 keys for 5 sockets
5	5723 50	○ White with red shutter
5	5728 50	● Magnesium with red shutter
5	5728 63	● Champagne with red shutter
5	5728 62	● Soft Alu with red shutter
		<b>UTP</b> 1 module
10	5723 49	○ White
10	5728 49	● Magnesium
10	5728 65	● Champagne
10	5728 64	● Soft Alu
10	5723 58	○ White with orange shutter
10	5728 58	● Magnesium with orange shutter
10	5728 69	● Champagne with orange shutter
10	5728 68	● Soft Alu with orange shutter
10	5723 59	○ White with green shutter
10	5728 59	● Magnesium with green shutter
10	5728 67	● Champagne with green shutter
10	5728 66	● Soft Alu with green shutter
		<b>UTP with controlled access</b> 2 modules Supplied with 2 keys for 5 sockets
5	5723 57	○ White with red shutter
5	5728 57	● Magnesium with red shutter
5	5728 72	● Champagne with red shutter
5	5728 71	● Soft Alu with red shutter

Pack	Cat. Nos.	Cat. 6 sockets
		<b>UTP</b> 1 module
10	5723 02	○ White
10	5728 02	● Magnesium
10	5700 57	● Champagne
10	5710 57	● Soft Alu
10	5723 54	○ White with orange shutter
10	5728 54	● Magnesium with orange shutter
10	5728 74	● Champagne with orange shutter
10	5728 73	● Soft Alu with orange shutter
10	5723 55	○ White with green shutter
10	5728 55	● Magnesium with green shutter
10	5728 80	● Champagne with green shutter
10	5728 79	● Soft Alu with green shutter
		<b>UTP</b> 2 modules
10	5723 14	○ White - square version
10	5728 14	● Magnesium - square version
10	5700 59	● Champagne - square version
10	5710 59	● Soft Alu - square version
10	5723 24	○ White - round version
10	5728 24	● Magnesium - round version
10	5728 81	● Soft Alu - round version
		<b>FTP</b> 1 module
10	5723 22	○ White
10	5728 22	● Magnesium
10	5728 91	● Champagne
10	5728 90	● Soft Alu
		<b>STP shielded</b> 1 module
10	5723 23	○ White
10	5728 23	● Magnesium
10	5728 95	● Champagne
10	5728 94	● Soft Alu
		<b>Cat. 5e sockets</b>
		<b>UTP</b> 1 module
10	5723 03	○ White
10	5728 03	● Magnesium
10	5700 58	● Champagne
10	5710 58	● Soft Alu
		<b>FTP</b> 1 module
10	5723 04	○ White
10	5728 04	● Magnesium
10	5729 08	● Champagne
10	5729 07	● Soft Alu