



5722 72



5722 83



5722 70



5722 84



5722 76

 Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Female 2 RCA sockets
		Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder
		Connection on screw terminals
		1 module
1	5722 72	○ White
1	5727 72	● Magnesium
1	5724 95	● Champagne
1	5724 94	● Soft Alu

Pack	Cat. Nos.	Female 3 RCA sockets
		Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder
		Connection on screw terminals
		1 module
1	5722 73	○ White
1	5727 73	● Magnesium
1	5724 97	● Champagne
1	5724 96	● Soft Alu

Pack	Cat. Nos.	3-pole XLR sockets
		For the stereo connection of any peripheral, microphone, mixing console
		Recommended cable : 1 audio pair 0.14 to 0.5 mm ² shielded Max. cable length : 50 m (beyond this an audio amplifier is recommended)
		2 modules
		XLR female
1	5722 83	○ White
1	5727 83	● Magnesium
1	5724 99	● Champagne
1	5724 98	● Soft Alu
		XLR male
1	5722 77	○ White
1	5727 77	● Magnesium

Pack	Cat. Nos.	Loudspeaker sockets
		4 mm ² terminals
		1 module
10	5722 70	○ White
10	5727 70	● Magnesium
10	5726 97	● Champagne
10	5726 96	● Soft Alu
		2 modules
10	5722 80	○ White
10	5727 80	● Magnesium
10	5726 99	● Champagne
10	5726 98	● Soft Alu
		Attenuators
		100 V - 25 W Allow to adjust power to 25 W from a balanced 100 V loudspeaker line
		2 modules
1	5722 84	○ White
1	5727 84	● Magnesium

Pack	Cat. Nos.	Other audio and video sockets
		Female BNC 75 sockets
		Provide the composite video link for any peripheral device such as a DVD drive, camera, video recorder, etc
		Connection on screw terminals
		1 module
1	5722 76	○ White
1	5727 76	● Magnesium

 USB data sockets see **p. 22**
 MediaHub see **p. 27**
