

Hotel equipment

Arteor wiring devices round version



5732 95



5737 35



5725 67



5725 74



Support frames and surround plates selection charts **p. 30, 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 30) and surround plates (p. 32 to 35)

Pack	Cat. Nos.	Lighting control
10 10	5732 85 5737 85	Master switch 2 way double pole 20 AX - 250 V~ for general control : all ON / all OFF 2 modules ○ White ● Magnesium
10 10	5732 87 5737 87	Master push button 2 way 6 A - 250 V~ for general control : all ON/ all OFF 2 modules ○ White ● Magnesium
5 5	5732 95 5737 95	Switch for bed lights 2 x 2 way switch - 10 AX - 250 V~ 2 x 1 module ○ White ● Magnesium
5 5	5732 97 5737 97	Push button for bed lights 2 x 2 way push button - 6 A - 250 V~ 2 x 1 module ○ White ● Magnesium
10 10	5732 23 5737 23	Electric roller blinds control - 250 VA Double switch 10 A For direct control of a motor (mechanism with fixed positions) 2 modules ○ White ● Magnesium
10 10	5732 25 5737 25	Double push button 10 A For control via automatic box (N/O mechanism) 2 modules ○ White ● Magnesium
10 10	5732 35 5737 35	Curtain control - 250 VA Double switch 10 A For direct control of a motor (mechanism with fixed positions) 2 modules ○ White ● Magnesium
10 10	5732 37 5737 37	Double push button 10 A For control via automatic box (N/O mechanism) 2 modules ○ White ● Magnesium

Pack	Cat. Nos.	Hotel bedroom call indicators
5 5 5	5720 67 5725 67 5727 31	Enable the resident to inform hotel staff of the room status Two settings are possible : - Do not disturb - Please clean the room 2 x 1 module Indicator for corridor Indicator lamp and bell push Installed in the corridor, display calls Supplied with LED ○ White ● Magnesium ● Soft Alu
5 5 5	5720 74 5725 74 5727 49	Internal control unit Allows the user to select the desired setting Supplied with LED ○ White ● Magnesium ● Soft Alu
10 10	5722 08 5722 48	Buzzers 230 V 2 modules ○ White ● Magnesium
1 1	5722 56 5727 56	Reading lights Fitted with maintenance-free LEDs LED colours : 3 000 K (neutral white) 230 V power supply - energy class A Screw terminals For installation in the bedhead Offers directional lighting Equipped with a flexible cable so the head can swivel Built-in dimmer Consumption 3-3 W Luminous flux 110 lumen (equivalent to 15 W incandescent) Service life 4 000 hours For installation in back box depth 40 mm min. 2 modules Round version ○ White ● Magnesium



RJ 45 and audio/video sockets,
p. 21-24

