

Synergy® white

dimmers



7311 51








7301 57




7300 49

Front plates : white thermoset
Terminal screws captive and backed off ready for cabling
Supplied with faceplate screw caps

Pack	Cat. Nos.	
1	7311 51	<p>Push on/off rotary universal dimmer 5-300 W / 100-240 V\sim - 50/60 Hz</p> <p>Conform to BS EN 60669-2-1 Flush mounting back box : min. 40 mm deep Equipped with overvoltage and short-circuit protection Screw terminals. For all types of lamps : - dimmable LEDs : 5 W to 75 W - dimmable compact fluorescent lamps : 5 W to 75 W - halogen with ferromagnetic or electronic transformer : 5 VA to 300 VA - fluorescent tube - ballast : 5 VA to 300 VA - halogen and incandescent 230 V : 5 W to 300 W When switched on, gradually (2 seconds) lights up at the level set before last switch-off Nominal plate dimensions : 86 x 86 mm</p>  1 gang - 2 way push switch
1	7301 50	<p>Push on/off rotary dimmer 1000 W 100-240 V / 50-60 Hz</p> <p>Conform to BS EN 60669-1 - Flush mounting back box : min. 40 mm deep - 60-1000 W (230 V) - 60-500 W (127 V) for incandescent and halogen lamps 60-600 VA (230 V) - 60-300 VA (127 V) for halogen lamps with electronic transformers 60-100 VA (230 V) - 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers Nominal plate dimensions : 86 x 86 mm</p>  1 gang

Pack	Cat. Nos.	
1	7301 56	<p>Push on/off rotary dimmers - 230 V\sim - electronic type</p> <p>Conform to BS EN 60669-2-1 : 2000 and BS EN 55015</p> <p>Rotary dimming and push on/off For use with 230 V AC - 50-60 Hz Not suitable for fluorescent load Flush mounting back box : min. 25 mm deep</p> <p>Dimmers for use with tungsten filament lamps, good quality wire-wound transformers for low voltage loads</p> <p>Nominal plate dimensions : 86 x 86 mm</p>  1 gang - 2 way 50 Hz 40 W-400 W push on/off rotary
1	7301 57	<p> 2 gang - 2 way 50 Hz 40 W-400 W push on/off rotary</p> <p>Nominal plate dimensions : 86 x 146 mm</p>
1	7300 49	<p> 4 gang - 2 way 50 Hz 40 W-400 W push on/off rotary</p>

For non-rotary dimmers, use Arteor modules with Synergy carrier plates
Contact us on +44 (0) 345 605 4333

 Flush and surface mounting back boxes **p. 55**



 Thermostat solutions **p. 16**

