

Synergy® white

fused connection units



7300 34



7300 35 + optional red LED power indicator (Cat. No. 7300 58 p. 54)



7300 30



Bespoke and standard engraving available **p. 57**



7300 36



7301 36



7300 33

Technical information **p. 56**

Front plates : white thermoset
Terminal screws captive and backed off ready for cabling
Supplied with faceplate screw caps

Pack	Cat. Nos.	Fused connection units 13 A - 250 V~
		<p>Conform to BS 1363 - Part 4 : 1995</p> <p>Options available as standard with red 'power on' LED indicator</p> <p>LED 'power on' upgrade pack also available (p. 54)</p> <p>Fused 13 A (fuse supplied)</p> <p>Fuse drawer retained by quarter turn catch, drawer padlockable in open position for safety</p> <p>To obtain flush to wall external cord connection on standard depth Cat. Nos. use cord outlet accessory box Cat. No. 7300 53 (p. 54)</p> <p>Flush mounting back box : min. 25 mm deep</p> <p>Nominal plate dimensions : 86 x 86 mm</p> <p>Switched</p>
10	7300 34	Switched, DP
10	7300 35	Switched, DP with red LED power indicator
10	7300 36	Switched, DP with cord outlet
10	7300 37	Switched, DP with cord outlet + red LED power indicator
10	7301 36	Switched, DP - deep plate with bottom cord outlet

Pack	Cat. Nos.	Fused connection units 13 A - 250 V~ (continued)
		Unswitched
10	7300 30	Unswitched
10	7300 31	Unswitched with red LED power indicator
10	7300 32	Unswitched with cord outlet
10	7300 33	Unswitched with cord outlet + red LED power indicator

Red power indicator LED pack p.54

Flush and surface mounting back boxes **p. 55**

