

# Synergy® white

## TV, telephone and data sockets



7300 40



7300 42



7300 50



7300 43



7300 45



7300 57

Front plates : white thermoset  
Supplied with faceplate screw caps

Pack	Cat. Nos.	TV, radio and satellite sockets
10	7300 40	Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm Screened TV – single, male Non-isolated
1	7300 41	Screened satellite – single, 'F' type
10	7300 42	Screened TV + FM Isolated
1	7300 43	Screened TV + FM + satellite, 'F' type
1	7300 45 <sup>1</sup>	Nominal plate dimensions : 86 x 146 mm Quad outlet, TV, radio + 2 satellite + TV return with secondary telephone outlet

Pack	Cat. Nos.	Telephone sockets
10	7300 50 <sup>1</sup>	Shuttered Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm Single master
10	7300 51 <sup>1</sup>	Single secondary
10	7300 54	Single RJ11/12

Pack	Cat. Nos.	Data sockets
1	7300 56	CAT 6 compliant UTP Rapid cable connection Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 86 mm RJ45 – single
1	7300 57	RJ45 – double

**Also available :**  
Euro module plates for 25 x 50 mm data modules (p. 54)

Pack	Cat. Nos.	Media plate (monobloc)
1	8201 42	Comprising : • 2 x independent satellite feeds • 1 x terrestrial TV socket suitable for analogue and digital signals • 1 x video return • 1 gang x 2 modules Arteor carrier plate with blanks, suitable for Arteor mechanisms (telephone, HDMI, RJ45, RCA) • 2 x Synergy 2 gang switched double pole 13 A sockets To be used with back box Cat. No. 8204 58 (see below) Nominal plate dimensions : 206 x 267 mm White (metal)

Pack	Cat. Nos.	Back box for media plate
1	8204 58	Dimensions : 194 x 254 x 35 mm With phase barrier Material : grey epoxy coated steel 35 mm deep box

Flush and surface mounting  
back boxes **p. 55**



1 : Not suitable for use in Republic of Ireland.