

# Synergy® Authentic

## British standard socket outlets



Slim front plate :



BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L







PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Socket outlets 13 A - 250 V~
		Conform to BS 1363 : Part. 2 With safety shutter mechanism Flush mounting back box : min. 25 mm deep ASTA licence
		<b>1 gang unswitched</b> Nominal plate dimensions : 86 x 86 mm
1	8330 65	 ● Brushed stainless steel
1	8332 65	● Polished stainless steel
1	8334 65	● Gold
		<b>2 gang unswitched</b> Nominal plate dimensions : 86 x 146 mm
1	8330 75	 ● Brushed stainless steel
1	8332 75	● Polished stainless steel
1	8334 75	● Gold

Pack	Cat. Nos.	Double pole socket outlets 13 A - 250 V~
		Conform to BS 1363 : Part. 2 With safety shutter mechanism Flush mounting back box : min. 25 mm deep ASTA licence
		<b>1 gang switched</b> Nominal plate dimensions : 86 x 86 mm
1	8330 60	 ● Brushed stainless steel
1	8332 60	● Polished stainless steel
1	8334 60	● Gold
		<b>1 gang switched with blue LED power indicator</b> Nominal plate dimensions : 86 x 86 mm
1	8330 61	 ● Brushed stainless steel
1	8332 61	● Polished stainless steel
1	8334 61	● Gold
		<b>2 gang switched</b> Nominal plate dimensions : 86 x 146 mm
1	8330 70	 ● Brushed stainless steel
1	8332 70	● Polished stainless steel
1	8334 70	● Gold
		<b>2 gang switched with blue LED power indicators</b> Nominal plate dimensions : 86 x 146 mm
1	8330 71	 ● Brushed stainless steel
1	8332 71	● Polished stainless steel
1	8334 71	● Gold
		<b>2 gang switched outboard for standard and clean earth applications</b> Nominal plate dimensions : 86 x 146 mm
1	8330 74	 ● Brushed stainless steel
1	8332 74	● Polished stainless steel
1	8334 74	● Gold
		<b>Key switched socket outlets 13 A - 250 V~</b>
		Conform to BS 1363 - Part. 2 : 1995 Flush mounting back box : min. 35 mm deep Nominal plate dimensions : 86 x 146 mm
1	8216 57	 ● Brushed stainless steel
1	8216 58	● Polished stainless steel
1	8216 59	● Gold