

# Synergy® Authentic

## fan switch and double pole switches



8334 09



8330 10



8332 16



8334 12



8330 22



8332 23



8334 21

Slim front plate :





BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L




PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	3 pole fan switch 10 A - 250 V~
1	8330 09	Conform to BS EN 60669-1 : 2000 With integrated padlockable safety block in OFF position Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>
1	8332 09	
1	8334 09	
<b>Double pole switches 20 A - 250 V~</b> Conform to BS EN 60669-1 Flush mounting back box : min. 25 mm deep Use cord outlet accessory Cat. No. 7300 53 (p.54) for external cord outlet Nominal plate dimensions : 86 x 86 mm		
1	8330 10	<b>DP switch</b>  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>
1	8332 10	
1	8334 10	
1	8330 16	<b>DP switch + cord outlet + blue LED power indicator</b>  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>
1	8332 16	
1	8334 16	
1	8330 12	<b>DP switch + blue LED power indicator</b>  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>
1	8332 12	
1	8334 12	

Pack	Cat. Nos.	Double pole switches 45 A - 250 V~
Conform to BS EN 60669-1 Flush mounting back box : min. 45 mm deep		
<b>1 gang switch</b> Nominal plate dimensions : 86 x 86 mm  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>		
1	8330 22	<b>1 gang switch + blue LED power indicator</b> Nominal plate dimensions : 86 x 86 mm  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>
1	8332 22	
1	8334 22	
<b>1 gang switch + blue LED power indicator large plate</b> Nominal plate dimensions : 146 x 86 mm  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Gold</li> </ul>		
1	8330 21	
1	8332 21	
1	8334 21	