

## Synergy® Authentic

cooker control units and fused connection units



8332 29



8334 37

Slim front plate :

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Cooker control units - 250 V~
		Conform to BS 4177 : 1992 Flush mounting back box : min. 47 mm deep Nominal plate dimensions : 86 x 146 mm
		<b>45 A DP switch + 13 A DP switched socket outlet with blue LED power indicators</b>
1	8330 29	● Brushed stainless steel
1	8332 29	● Polished stainless steel
1	8334 29	● Gold
		<b>Fused connection units 13 A - 250 V~</b>
		Conform to BS 1363 : Part 4 Front cable outlet with cord grip Fuse supplied Locked captive fuse carrier (padlockable) Flush mounting back box : min. 25 mm deep Nominal plate dimensions : 86 x 86 mm
		<b>Unswitched with cord outlet</b>
1	8330 32	● Brushed stainless steel
1	8332 32	● Polished stainless steel
1	8334 32	● Gold
		<b>Unswitched without cord outlet</b>
1	8330 30	● Brushed stainless steel
1	8332 30	● Polished stainless steel
1	8334 30	● Glossy gold
		<b>Unswitched with blue LED power indicator</b>
1	8330 31	● Brushed stainless steel
1	8332 31	● Polished stainless steel
1	8334 31	● Gold
		<b>Unswitched with blue LED power indicator + cord outlet</b>
1	8330 33	● Brushed stainless steel
1	8332 33	● Polished stainless steel
1	8334 33	● Gold
		<b>DP switched without cord outlet</b>
1	8330 34	● Brushed stainless steel
1	8332 34	● Polished stainless steel
1	8334 34	● Gold
		<b>DP switched with blue LED power indicator</b>
1	8330 35	● Brushed stainless steel
1	8332 35	● Polished stainless steel
1	8334 35	● Gold
		<b>DP switched with blue LED power indicator + cord outlet</b>
1	8330 37	● Brushed stainless steel
1	8332 37	● Polished stainless steel
1	8334 37	● Gold

## Synergy® Authentic

shaver sockets, cable outlets, blanking plates and cord outlets



8332 90



8330 19



8334 95

Slim front plates :

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Shaver sockets
		Conform to BS EN 61558-2-5 Suitable for use with European, British and Australian 2 pin plugs Rating : 20 VA IP 24 Screwless live and neutral terminals Flush mounting back box : min. 45 mm deep Nominal plate dimensions : 146 x 86 mm
		<b>230/120 V~ - 50/60 Hz</b>
1	8330 90	● Brushed stainless steel
1	8332 90	● Polished stainless steel
1	8334 90	● Gold
		<b>Cable outlets</b>
		Conform to BS 5733 Fitted clamp and outlet membrane With terminal block Nominal plate dimensions : 86 x 86 mm
		<b>20 A - 250 V~</b>
1	8330 19	● Brushed stainless steel
1	8332 19	● Polished stainless steel
1	8334 19	● Gold
		<b>45 A - 250 V~</b>
1	8330 26	● Brushed stainless steel
1	8332 26	● Polished stainless steel
1	8334 26	● Gold
		<b>Blanking plates</b>
		<b>1 gang</b> Nominal plate dimensions : 86 x 86 mm
1	8330 95	● Brushed stainless steel
1	8332 95	● Polished stainless steel
1	8334 95	● Gold
		<b>2 gang</b> Nominal plate dimensions : 86 x 146 mm
1	8330 96	● Brushed stainless steel
1	8332 96	● Polished stainless steel
1	8334 96	● Gold
		<b>Cord outlets</b>
		<b>1 gang</b> Nominal plate dimensions : 86 x 86 mm
1	8330 52	● Brushed stainless steel
1	8332 52	● Polished stainless steel
1	8334 52	● Gold