

Synergy® Sleek Design

double pole switches



8320 10



8322 16



8324 12



8324 23

Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Double pole switches 20 A - 250 V \sim
		Conform to BS EN 60669-1 Flush mounting back box : min. 35 mm deep Supplied with 1 gang side extension (3 mm thick) in case extra wiring space is needed Nominal plate dimensions : 86 x 86 mm
		Double pole switch
1	8320 10	Brushed stainless steel
1	8322 10	Polished stainless steel
1	8324 10	Gold
		Double pole switch + cord outlet
1	8320 16	Brushed stainless steel
1	8322 16	Polished stainless steel
1	8324 16	Gold
		Double pole switch + blue LED power indicator
1	8320 12	Brushed stainless steel
1	8322 12	Polished stainless steel
1	8324 12	Gold

Pack	Cat. Nos.	Double pole switches 45 A - 250 V \sim
		Conform to BS EN 60669-1 Flush mounting back box : min. 47 mm deep Red rocker Nominal plate dimensions : 86 x 86 mm
		Double pole switch + blue LED power indicator
1	8320 23	Brushed stainless steel
1	8322 23	Polished stainless steel
1	8324 23	Gold