

Synergy® Sleek Design

cooker control units, fused connection units and cable outlets



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Cooker control units - 250 V~
1	8320 29	Conform to BS 4177 : 1992 Flush mounting back box : min. 47 mm deep Nominal plate dimensions : 86 x 146 mm 45 A Double pole switch + 13 A DP switched socket outlet - with blue LED power indicator ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 29	
1	8324 29	

Pack	Cat. Nos.	Fused connection units unswitched 13 A - 250 V~
1	8320 32	Conform to BS 1363 : Part. 4 Front cable outlet with cord grip. Fuses supplied Locked captive fuse carrier (padlockable) Flush mounting back box : min. 35 mm deep Supplied with 1 gang side extension (3 mm thick) in case extra wiring space is needed Nominal plate dimensions : 86 x 86 mm Unswitched - with cord outlet ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 32	
1	8324 32	

Pack	Cat. Nos.	Fused connection units switched 13 A - 250 V~
1	8320 35	Conform to BS 1363 : Part. 4 Front cable outlet with cord grip. Fuses supplied Locked captive fuse carrier (padlockable) Flush mounting back box : min. 35 mm deep Supplied with 1 gang side extension (3 mm thick) in case extra wiring space is needed Nominal plate dimensions : 86 x 86 mm Double pole switched - without cord outlet ● Brushed stainless steel ● Polished stainless steel ● Gold Double pole switched - with blue LED power indicator + cord outlet ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 35	
1	8324 35	

Pack	Cat. Nos.	Cable outlets
1	8320 19	Conform to BS 5733 Fitted with clamp and outlet membrane With terminal block Nominal plate dimensions : 86 x 86 mm 20 A - 250 V~ ● Brushed stainless steel ● Polished stainless steel ● Gold 45 A - 250 V~ ● Anthracite grey colour (plastic)
1	8322 19	
1	8324 19	
1	8320 26	

Synergy® Sleek Design

hotel equipment



Sleek design

BSS : Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS : Plates made of Stainless Steel + rust resistance

G : Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat. Nos.	Shaver sockets
1	8320 90	Conform to BS EN 61558-2-5 Suitable for use with European, British, American and Australian 2 pin plugs. Rating : 20 VA. IP 24 Screwless live and neutral terminals Flush mounting back box : min. 45 mm deep Supplied with 2 gang side extension (3 mm thick) in case extra wiring space is needed Nominal plate dimensions : 146 x 86 mm 230 V / 120 V - 50/60 Hz ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8322 90	
1	8324 90	

Pack	Cat. Nos.	Key card switch 230 V
1	8321 00	For energising a circuit by inserting a key fob or a smart card (access card for a hotel room) Example of use : hotel room power supply only when guest is present Time delay of approx. 30 sec. after card removal To be equipped with a single pole latching relay or contactor Nominal plate dimensions : 86 x 86 mm ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8323 00	
1	8325 00	

Pack	Cat. Nos.	Hotel call indicator DND/Please clean
1	8321 01	Indicator for corridor Indicator lamp and bell push Installed in the corridor, displays calls Nominal plate dimensions : 86 x 86 mm ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8323 01	
1	8325 01	

Pack	Cat. Nos.	Hotel call indicator - internal room control
1	8321 02	Internal control unit Allows the user to select the desired setting Supplied with LED Nominal plate dimensions : 86 x 86 mm ● Brushed stainless steel ● Polished stainless steel ● Gold
1	8323 02	
1	8325 02	