

Synergy® metalclad

socket outlets



7338 65



7338 75



7338 89



Unique clam type fit

Finish : grey epoxy coated steel
Terminal screws captive and backed off ready for cabling
Supplied complete with close fit surface mounting back box with knockouts

Pack	Cat. Nos.	Unswitched and key switched socket outlets 13 A - 250 V~	Pack	Cat. Nos.	RCD sockets 13 A - 250 V~
10	7338 65	<p>Conform to BS 1363 - Part 2 : 1995 2 earth terminals Nominal dimensions : 86 x 86 x 43 mm</p> <p>1 gang – unswitched</p> <p>Nominal dimensions : 86 x 146 x 43 mm</p>	1	7338 80	<p>Conform to BS 7288 : 1990 and BS 1363 - Part 2 : 1995 Conventional earth pin release shutter Maximum operating current 16 A Electronic RCD module with a membrane switch for 'test and reset' Flush mounting back box : min. 25 mm deep</p> <p>DP 30 mA - active - trips in the event of a power failure - suitable in applications where automatic restoration of supply would be hazardous, e.g. machinery, power tools</p> <p>Nominal dimensions : 86 x 86 x 43 mm 1 gang</p>
5	7338 75	<p>2 gang – unswitched</p>	1	7338 82	<p>Nominal dimensions : 86 x 146 x 43 mm 2 gang</p>
5	7338 88	<p>Conform to BS 546 : 1950 Nominal dimensions : 86 x 86 x 43 mm</p> <p>1 gang – unswitched</p>	1	7338 81	<p>DP 30 mA - passive - does not trip in the event of a power failure - suitable in applications where automatic restoration of supply is required, e.g. fridge, freezer, unmanned areas</p> <p>Nominal dimensions : 86 x 86 x 43 mm 1 gang</p>
5	7338 89	<p>1 gang – switched</p>	1	7338 83	<p>Nominal dimensions : 86 x 146 x 43 mm 2 gang</p>

Surface mounting back boxes with or without knockouts
p. 77

