

Synergy® metalclad

fused connection units and control switches



Finish : grey epoxy coated steel
Terminal screws captive and backed off ready for cabling
Supplied complete with close fit surface mounting back box with knockouts

Pack	Cat. Nos.	Fused connection units 13 A - 250 V~
		Conform to BS 1363 - Part 4 : 1995 Fused 13 A (fuse supplied) Fuse drawer retained by quarter turn catch, drawer padlockable in open position for safety Nominal dimensions : 86 x 86 x 43 mm
		Switched
5	7338 34	Switched, DP
5	7338 35	Switched, DP with red LED power indicator
5	7338 36	Switched, DP with cord outlet
5	7338 37	Switched, DP with cord outlet + red LED power indicator
		Unswitched
5	7338 30	Unswitched
5	7338 31	Unswitched with red LED power indicator
5	7338 32	Unswitched with cord outlet
5	7338 33	Unswitched with cord outlet + red LED power indicator

Pack	Cat. Nos.	Double pole switches 20 A - 250 V~
		Conform to BS EN 60669-1 Nominal dimensions : 86 x 86 x 43 mm
5	7338 10	20 A DP
5	7338 16	20 A DP with cord outlet + red LED power indicator
5	7338 12	20 A DP + red LED power indicator
		Cable outlet 20 A - 250 V~
		Conform to BS 5733 : 1995 Nominal dimensions : 86 x 86 x 43 mm
5	7338 19	20 A – with terminal block and outlet gland
		Double pole switches 45 A - 250 V~
		Conform to BS EN 60669-1 Red rocker Nominal dimensions : 146 x 86 x 43 mm
5	7338 21	45 A DP + red LED power indicator

Surface mounting back boxes with or without knockouts
p. 77

