

LB PLUS busbar trunking systems

selection chart

	25 A				40 A		63 A
	2 conductors	4 conductors	6 conductors	8 conductors	4 conductors	8 conductors	4 conductors
LB PLUS STRAIGHT LENGTHS – TYPE A	252	254	256	258	404	408	634
3 m length – 2 outlets	75150101	75160101	–	–	75200101	–	–
3 m length – 4 outlets	–	75160102	–	–	75200102	–	–
3 m length – 2 + 2 outlets	–	–	75170101	75180101	–	75220101	75240101
3 m length – 4 + 4 outlets	–	–	–	75180102	–	75220102	75240102
1.5 m length – 2 outlets	75200111		–	–	75200111	–	–
1.5 m length – 1 + 1 outlets	–	–	75220111		–	75220111	75240111
LB PLUS STRAIGHT LENGTHS – TYPE B	252	254	256	258	404	408	634
3 m length – 4 outlets	75350102H	75360102H	–	–	75400102H	–	–
3 m length – 6 outlets	–	75360103H	–	–	75400103H	–	–
3 m length – 4 + 4 outlets	–	–	75370101H	75380101H	–	75420101H	75440101H
3 m length – 6 + 6 outlets	–	–	–	75380102H	–	75420102H	75440102H
1.5 m length – 2 outlets	75400111H		–	–	75400111H	–	–
1.5 m length – 1 + 1 outlets	–	–	75420111H		–	75420111H	75440111H
FEED UNITS	252	254	256	258	404	408	634
RH feed unit + end cover (reduced dimensions)	75201003		75221003		75201003	75221003	75241003
LH feed unit + end cover (reduced dimensions)	75201004		75221004		75201004	75221004	75241004
Fast fit – feed unit RH	75161001		–	–	–	–	–
Fast fit – feed unit LH	75161002		–	–	–	–	–
Centre feed unit + end covers (reduced dimensions)	75201151		75221151		75201151	75221151	75241151
FLEXIBLE JOINT	75201263		75221263		75201263	75221263	75241263
BRACKETS AND SUSPENSIONS	252	254	256	258	404	408	634
60 kg suspension bracket	75003000 (for TYPE A)			and	75003004 for (TYPE B)		
Hook for lamp				75003001			
Ring				75003002			
Pigtail for chain				75003005			
5 m steel cable with self locking clamp (TYPE B)				75003008 (TYPE B only)			
Bracket with 3 m steel cable (TYPE A)				75003009 (TYPE A only)			
CABLE CHANNEL	252	254	256	258	404	408	634
PVC cable channel with cover (3 m)				71000104			
Bracket for cable channel				75003006			

10 A SINGLE PHASE TAP-OFFS	252	254	256	258	404	408	634
10 A plug with 1 m cable - L1-N	75005011						
10 A plug with 1 m cable - L2-N	–	75005012					
10 A plug with 1 m cable - L3-N	–	75005013					
10 A plug with 1 m cable - L-N2	–	75005014					
10 A plug with 3 m cable - L1-N	75005021						
10 A plug with 3 m cable - L2-N	–	75005022					
10 A plug with 3 m cable - L3-N	–	75005023					
10 A plug with 3 m cable - L-N2	–	75005024					
16 A PHASE SELECTION TAP-OFFS	252	254	256	258	404	408	634
16 A plug (unfused)	75005000						
16 A plug + 1 x (5 x 20)	75005100						
16 A plug + 1 x (CH8)	75005200						
16 A PRE-WIRED TAP-OFFS	252	254	256	258	404	408	634
SP & N with 1·5 m cable and 6·3 A fuse - L1-N	750051001L1						
SP & N with 1·5 m cable and 6·3 A fuse - L2-N	–	750051001L2					
SP & N with 1·5 m cable and 6·3 A fuse - L3-N	–	750051001L3					
SP & N with 1·5 m cable and 6·3 A fuse - L-N2	–	750051001LN2					
DP & N with 1·5 m cable and 2 x 6·3 A fuse - L1+L3-N	–	7500510014C					
SP & N with 3 m cable and 6·3 A fuse - L1-N	750051003L1						
SP & N with 3 m cable and 6·3 A fuse - L2-N	–	750051003L2					
SP & N with 3 m cable and 6·3 A fuse - L3-N	–	750051003L3					
SP & N with 3 m cable and 6·3 A fuse - L-N2	–	750051003LN2					
DP & N with 3 m cable and 2 x 6·3 A fuse - L1+L3-N	–	7500510034C					
THREE-PHASE TAP-OFFS – 16 - 25 A	252	254	256	258	404	408	634
16 A 3 phase (unfused)	–	75005005					
25 A 3 phase (unfused)	–	75007005					
25 A 3 phase + 3 x (CH8)	–	75007205					
25 A 3 phase + 3 x (CH8) + 4 DIN BOX	–	75007206					
25 A 3 phase + (unfused) + 8 DIN BOX	–	75007207					
25 A 3 phase + (unfused) + 4 DIN BOX	–	75007006					
TAP-OFF ACCESSORIES	252	254	256	258	404	408	634
16 A mobile contact	75105000						
Window kit code	75105001						