


- Commande pour interrupteur sectionneur rotatif
- Bediening voor draaiende scheidelastschakelaar
- Control for rotary isolating switch
- Steuerung für Drehlasttrennschalter
- Mando por interruptor seccionador rotativo
- Comando per interruttore sezionatore rotativo

221 01/09/11/31/34/36/41/49/51 - 221 78




- Assemblage encastré
- Ingebouwde assemblage


221 01/09/11

- Flush-mounting assembly
- Unterputz-Montage

- Ensamblaje empotrado
- Assemblaggio incassato



1:1




- Assemblage encastré - Ø 22
- Ingebouwde assemblage - Ø 22

- Flush-mounting assembly - Ø 22
- Unterputz-Montage - Ø 22

- Ensamblaje empotrado - Ø 22
- Assemblaggio incassato - Ø 22

221 31/34/36




- Commande frontale extérieure
- Frontale externe bediening

- External front control
- externe Stirnsteuerung

- Mando frontal exterior
- Comando frontale esterno


221 41/49/51



- Assemblage
- Assemblage



- Assembly
- Zusammenbau

- Ensamblaje
- Assemblaggio



	Y (mm)	X (mm)
3 - 4 P	84	$116 \leq X \leq 240$
3 P + OF	94	$125 \leq X \leq 250$

	Y (")	X (")
3 - 4 P	3,31	$4,57 \leq X \leq 9,45$
3 P + OF	3,70	$4,92 \leq X \leq 9,84$



- Fermeture boîtier
- Sluiting behuizing

- Box closure
- Gehäuseverschluß

- Cierre de la caja
- Chiusura cassetta

221 78

