


Arteor™

Ref . No. : 572543

20AX SWITCH 3G1G 1W2M

Date : 01.11.2021

Rev.1

**1. USE**

General lighting control mechanism, Gadgets power control mechanism.

2.Type

One Way Switch (Square) Double Pole

No. of modules : 2

Colour : Magnesium

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 45 mm

Height :45 mm

Depth : 42 mm

Weight (g) : 46.50

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 4mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Terminal Plate : Polycarbonate

Plunger : Polycarbonate

Tip Terminal : Brass with Silver plated

Pivot Terminal : Brass with Silver plated

Screws : Steel with Zinc Plating

Rocker spring : Stainless steel

Transmitter : Polypropylene FR

Contact Tip : Silver

Moving Contact : Brass

6.2 Electricals Characteristics

Voltage :230V AC

Current : 20A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854