


ArteorTM
Ref . No. : 573611
20A Switch SP 1Mod. 2Way with Indicator
Date : 19/10/2021
Rev.1

1. USE

General lighting control mechanism, Gadgets power control mechanism.

2.Type

Two way switch (square) single pole

No. of modules : 1

Colour : Magnesium

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 22.5 mm

Height : 45 mm

Depth : 42.2 mm

Weight (g) : 24.50

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch operating mechanically by rocker toggling

6.TECHNICAL CHARACTERISTICS
6.1 Material Characteristics

Rocker: Polycarbonate

Base: Polycarbonate

Basket: Polypropylene FR

Contact Terminal: Brass Unplated

Pivot Terminal: Brass Unplated

Screws: Steel with Zinc Plating

Cover: Polypropylene FR

Plunger: Polycarbonate

Rocker spring: Stainles steel

Transmitter: Polypropylene FR

Contact Tip: Silver

Moving Contact: Brass

Lens: Polycarbonate

6.2 Electricals Characteristics

Voltage :230VAC

Current : 20A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854