

Mylinec™
Ref . No. : 675526
32A DP Switch 2M with indicator
Date : 04/12/2017
Rev.1

1. USE

General lighting control mechanism .

2.Type

One Way Switch double pole

No. of modules : 2

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 52 mm

Height : 57.2 mm

Depth : 45 mm

Weight (g) : 61

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6.0mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6. TECHNICAL CHARACTERISTICS
6.1 Material Characteristics

Rocker : Polycarbonate

Front cover : Polycarbonate

Lens : Polycarbonate red

Base : Polypropylene

Contacts : Copper with silver plating

Terminal : Brass with silver plating

Plunger : PA66+20%SI+PTFE

Screws : Brass with Tin plating

Plunger spring : Stainless steel

Contact tip : Silver

Moving contact : Copper with silver tip

6.2 Electricals Characteristics

Voltage : 230V AC

Current : 32A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854