


MylinecTM

Ref . No. : 675593

10AX Switch SP 1M 2Way - White

Date :31-01-2024

Rev.1

**1. USE**

General lighting, appliance, Gadgets power control mechanism.

2.Type

Two way switch single pole

No. of modules : 1

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 28 mm

Height :57.2 mm

Depth :35 mm

Weight (g) : 22

4.CONNECTION

Terminal : with screws

Capacity : 0.75mm² to 1.5mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Front Cover :Polycarbonate

Base : Polypropylene

Contact Terminal : Brass

Pivot Terminal : Brass

Screws : Brass

Rocker spring : Stainless steel

Transmitter : Polypropylene + Masterbatch

Contact Tip : Silver

Moving Contact : Brass

Bimetal tip for Moving Contact : Silver

Plastic enclosure for current carrying parts : Self - extinguishing : 850° C / 30 s.

6.2 Electricals Characteristics

Voltage : 230V AC

Current : 10AX

7.CONFORMITY - APPROVALS

As per IS : 3854