**PRODUCT TECHNICAL DATA SHEET**

| Lyncus TM | Ref . No. : 677206 | |
|---|---|---|
| **10A SWITCH 2W2M WHITE** | Date : 20/03/2019 | Rev.1 |



**1. USE**

General lighting control mechanism .

**2.Type**

Two Way Switch (Square ) Single pole
No. of modules : 2
Colour : White
Mounting : Flush and Surface - mounted

**3.OVERALL DIMENSIONS**

Width : 45 mm
Height :45 mm
Depth :33.6 mm
Weight (g) : 20

**4.CONNECTION**

Terminal : with screws
Capacity : 0.75mm$^2$ to 1.5mm$^2$
Stripping : 10 mm
Screwdriver : 4mm flat-blade up to 5 mm

**5.OPERATION**

Switch with rocker

**6.TECHNICAL CHARACTERISTICS**

**6.1 Material Characteristics**

Rocker : Polycarbonate
Base : Polypropelyne
Contact Terminal : Brass
Pivot Terminal : Brass
Screws : Steel with zinc plating
Rocker spring : Stainlessteel
Transmitter : Polypropelene
Contact Tip : Silver
Moving Contact : Brass

**6.2 Electricals Characteristics**

Voltage :230V AC
Current : 10A
Self - extinguishing : 850° C / 30 s.

**7.CONFORMITY - APPROVALS**

As per IS : 3854