


Lyncus™

Ref . No. : 677211

16A SWITCH 1W1M IND WHITE

Date : 20/03/2019

Rev.1

**1. USE**

General lighting control mechanism .

2.Type

One Way Switch with indicator (Square) Single Pole

No. of modules : 1

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 22.5 mm

Height :45 mm

Depth :33.6 mm

Weight (g) : 16.2

4.CONNECTION

Terminal : with screws

Capacity : 1.5mm² to 2.5mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Base : Polypropylene

Lens : Polycarbonate Red

Contact Terminal : Brass

Pivot Terminal : Brass

Screws : Steel with zinc plating

Rocker spring : Stainlesssteel

Transmitter : Polypropylene

Contact Tip : Silver

Moving Contact : Brass

6.2 Electricals Characteristics

Voltage :230V AC

Current : 16A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854