


Lyncus™

Ref . No. : 677217

32A DP SWITCH 2M IND White

Date : 20/03/2019

Rev.1

**1. USE**

General lighting control mechanism .

2.Type

One Way Switch with indicator (Square) Double Pole

No. of modules : 2

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 45 mm

Height :45 mm

Depth : 42.5 mm

Weight (g) : 28.5

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Base : Polycarbonate

Lens : Polycarbonate Red

Terminal : Brass with silver plating

Screws : Steel with zinc plating

Transmitter : PA66 + 20%SI + PTEE

Under cover : Polycarbonate

Plunger spring : Steel

Contact : Copper

6.2 Electricals Characteristics

Voltage :230V AC

Current : 32A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854