


Myrius™

Ref . No. : 679208

10A SWITCH 1 WAY 2M IND WHITE

Date : 07-05-2020

Rev.1

**1. USE**

General lighting control mechanism .

2.Type

One Way Switch with indicator (Square) Single Pole

No. of modules : 2

Colour : White

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 44.7 mm

Height :45.1 mm

Depth :37.8 mm

Weight (g) : 19.4

4.CONNECTION

Terminal : with screws

Capacity : 0.75mm² to 1.5mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Base : Polycarbonate

Lens: Polycarbonate homo natural

Contact Terminal : Brass

Pivot Terminal : Brass

Screws : Steel with Zinc plating

Rocker spring : Stainless steel

Transmitter : Polypropelene

Plunger: Polycarbonate

Contact Tip : Silver

Moving Contact : Brass

6.2 Electricals Characteristics

Voltage :230V AC

Current : 10A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854