


MyriusTM

Ref . No. : 679415

20A SWITCH 2 WAY 2M CHARCOAL GREY

Date : 07-05-2020

Rev.1

**1. USE**

General lighting control mechanism .

2.Type

Two Way Switch (Square) Single Pole

No. of modules : 2

Colour : Charcoal Grey

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 45.1 mm

Height :45.1 mm

Depth :42.4 mm

Weight (g) : 30.8

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6. TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate Grey

Cover : Polypropylene

Upper Base : Polycarbonate

Basket : Polypropylene

Plunger : Polycarbonate

Tip Terminal : Brass

Pivot Terminal : Brass

Screws : Steel with Zinc plating

Rocker spring : Stainless Steel

Transmitter : Polypropylene

Contact Tip : Silver

Moving Contact : Brass

6.2 Electricals Characteristics

Voltage :230V AC

Current : 20A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854