



Flush-mounting compact camera

391647 - 391648 391649 - 391651 391652 - 391653

Description

Flush-mounting compact colour camera. Flush mounted or wall installation using the dedicated accessories of the AXOLUTE, LIVING, LIGHT, LIGHT TECH residential series. Accessory for the wiring of the coaxial cable supplied. Power supply: 12 Vdc.

Related items

The camera must be completed with the accessories and the front cover plates of the AXOLUTE, LIVING, LIGHT, LIGHT TECH residential series. Refer to the corresponding catalogues.

Technical data

Sensor: 1/3" colour CCD
Optics: 3.7 mm (semi pin hole)


Interlaced: 2:1
Scanning standard: CCIR
Horizontal frequency: 15625 Hz
Vertical frequency: 50 Hz


Image elements: 537 (H) x 597 (V) Horizontal resolution: 380 TV lines

Video output: CVBS 1 Vpp 10% su 75 0hm, PAL compatible

Minimum illumination: 5 luxOperating temperature: $5-40\,^{\circ}\text{C}$ Power supply: $12\,\text{Vdc}$ Absorption: $120\,\text{mA}$







Legend

- 1. Integrated optics
- 2. Lens orientation adjustment: $+/-30^{\circ}$ vertical axis

 $+/-25^{\circ}$ horizontal axis

3. Microphone (PRESETTING - NOT OPERATING)

391647 - 391648 391649 - 391651 391652 - 391653

Connection and installation

