Indoor siren 4216

Description

The internal siren has a high sound pressure and a LED flasher which, when there is a power cut, can act as emergency light (only with battery 4238 installed). The siren is completely managed by a microcontroller, which checks all the conditions and informs the central unit of them via BUS.

Related items

4238 Lithium ion battery 7.4Vcc-850mAh

Technical data

Supply voltage 9.6 –14.5Vdc


Absorption 15mA Stand-by; 200mA max

Battery (4238 – not supplied) Lithium lons 7.4Vdc - 850mAh

Dimensional data

Size: 142 x 102 x 37mm (H x L x D)

Front view without cover



Legend

- 1. Microswitch for anti-tampering protection
- Emergency light setting jumper:
 Connected: emergency light OFF
 Disconnected: emergency light ON, it works only with connected battery (4238)
- 3. Buzzer connector
- 4. Anti-tampering microswitch
- 5. Anti-removal microswitch activation knock-out (to be fastened to the wall)
- 6. Buzzer: 98 dB at 1 m
- 7. Wall fixing holes
- $8. \ \ \, \text{Battery housing (4238-not supplied) 7.4vdc} 850\text{mAh}$
- 9. BUS connection clamps
- 10. Battery connector
- 11. 1W LED (flashing when there is an alarm or emergency light when there is a power cut, after installation of the battery, not supplied 4238)

