

# Datasheet

Vivo™

## Double Powerpoint 10A with dual USB Charger Mechanism Dual Type C

CAT. NO. EV777USBN2CWE, EV777USBN2CGR



A brand of **legrand**



EV777USBN2CWE



EV777USBN2CGR

Cat. No.	EV777USBN2CWE	EV777USBN2CGR
Colour	White (WE)	Dark Grey (GR)
Description	Vivo™ Double powerpoint with dual USB Charger Mechanism Type C	
Nominal Input Voltage	230-240 V a.c. 50 Hz	
Current Rating (GPO)	10 A	
Stand-by Power Consumption	75 mW	
Nominal Output Voltage	5 V d.c.	
Nominal Output Current	3 A	
Energy Efficiency	Level VI	
Protection Class	Class II	
Overload Protection (on output)	3.1 A	
Surge Protection	1750 A, 70 joules	
Operating Temperature	5°C to 25°C	
Dimensions (W x H x D)	119 x 85 x 50 mm	
Safety Standard	AS/NZS 61558.2.16, AS/NZS 4665	

Vivo™

# Double Powerpoint 10A with dual USB Charger Mechanism Dual Type C

CAT. NO. **EV777USBN2CWE, EV777USBN2CGR**



A brand of **legrand®**



Single product		
Cat. No.	Barcode	Dimensions (W x H x D)
EV777USBN2CWE	9321001524434	101 x 101 x 54 mm
EV777USBN2CGR	9321001524441	

Outer box (QTY 50)		
Cat. No.	Barcode	Dimensions (W x H x D)
EV777USBN2CWE	9321001524731	257 x 200 x 330 mm
EV777USBN2CGR	9321001524748	

## FEATURES

- 15 W Charging capacity over 2 ports.
- 2 x Type C USB port for latest devices and future releases.
- Capable of charging 2 smartphones simultaneously or 1 tablet at full speed.
- Suitable for smartphones, tablets, fitness bands and running watches.
- Suitable for all commercial and residential installations such as kitchens and bedside tables.
- Overload protection on output (USB circuit).
- Low standby power consumption: 75 mW.
- Indoor use only.

Legrand - Australia  
1300 369 777  
www.legrand.com.au  
ABN 31 000 102 661

Legrand - New Zealand  
0800 476 009  
www.legrand.co.nz

Refer to your group buying office, Legrand Sales Representative or  
Legrand Sales Office for pricing.

Please note: specifications are subject to change without prior notice.



LE14457AA

01/2025