

Data Sheet

VIVO™

Night Light – LED

CAT NO. EVNLIGHTWE



A brand of  legrand®



EVNLIGHTWE

Cat No.	EVNLIGHTWE
Description	Vivo™ Night Light – LED
Colour	White (WE)
Supply voltage	230-240V a.c.
Current rating	1.0W max
Plate size (W x H x D)	119 x 85 x 10mm
Mounting centres	84mm
Compliance	IEC 62094-1

VIVO™ Night Light – LED

CAT NO. **EVNLIGHTWE**



A brand of **legrand**



EVNLIGHTWE

- Suitable for studios, operation theatres and special access rooms
- Customise VIVO™ LED night lights by placing stickers on the window
- Choose between 2 levels of brightness: 0.2W or 1W
- LED - low energy consumption

Single product (Qty 1)		
Cat No.	Barcode	Dimensions (W x H)
EVNLIGHTWE	9321001466352	133 x 264mm

Inner box (Qty 6)		
Cat No.	Barcode	Dimensions (W x H x D)
EVNLIGHTWE	9321001467601	163 x 174 x 124mm

Outer box (Qty 72)		
Cat No.	Barcode	Dimensions (W x H x D)
EVNLIGHTWE	9321001468820	387 x 212 x 515mm

Glass and tile cut-out dimensions:



Legrand Australia
1300 369 777
www.hpm.com.au
ABN 31 000 102 661

Legrand New Zealand
0800 476 009
www.hpm.co.nz

Refer to your group buying office, Legrand Sales Representative or Legrand Sales Office for pricing.

Please note: specifications are subject to change without prior notice.