instant heat 2 and 4



2 heat lamp model: Cat R622/1AC 4 heat lamp model: Cat R622/2AC combination light, heater and exhaust fan for larger bathrooms and ensuites



- · Instantaneous heat at the flick of a switch
- Individual controls for each function
- HPM excel switch plate included
- More economical to run than most heaters
- 5 year warranty on materials and workmanship
- 2 year warranty on infra red lamps
- * Not available in New Zealand

specifications

Instant heat 2

Supply voltage: 230-240V a.c. 50Hz Max rating: 690W Motor rating: 40W Heat lamps: 2 x 275W Light lamps: 1 x 100W ES Air movement rate: 250m³/hr Projection into ceiling: 200mm Face protrusion: 40mm Impeller diameter: 230mm Hole cut-out size: 300mm dia Weight: 3.3kg Warranty: 5 years on material and workmanship 2 years on infra red lamps

IP Rating: NA



Instant heat 4

Supply voltage: 230-240V a.c. 50Hz Max rating: 1240W Motor rating: 40W Heat lamps: 4 x 275W Light lamps: 1 x 100W ES Air movement rate: 400m³/hr Projection into ceiling: 200mm Face protrusion: 40mm Impeller diameter: 230mm Hole cut-out size: 322mm square Weight: 4.5kg Warranty: 5 years on material and workmanship 2 years on infra red lamps IP Rating: NA

UHUON OF 405mm