Datasheet

Inspire Ceiling Fan Plywood with Light -1220mm CAT. NO. RCFTRI12H4WE, RCFTRI12H4BL











RCFTRI12H4WE

RCFTRI12H4BL

PRODUCT SPECIFICATIONS

Cat. No.	RCFTRI12H4WE	RCFTRI12H4BL	
Colour	White	Black	
Description	Inspire Ceiling Fan Plywood with Light, 4 Blades, 1220mm, 48", Hangsure		
Nominal Input Voltage	230 - 240 V a.c 50 Hz 50 W (Motor)		
Airflow	7680 m³/h		
Fan Power	Hi:50 W, Med:26 W, Low:13 W		
Fan Power Factor	0.95 @ 240 V a.c. 50 Hz		
Body Construction	Plywood		
LED LAMP Specification			
Lamp Type	with Integrated LED Light		
Wattage	15 W		
Lumen	900 lm		
Efficacy	60 lm/W		
CRI	80+		
Light Colour	Warm White, Cool White, Natural White		
Power Factor	0.5 @ 240 V a.c. 50 Hz		
Dimming	Non-Dimmable		
Warranty	3 Years		

Inspire Ceiling Fan Plywood with Light - 1220mm

CAT. NO. RCFTRI12H4WE, RCFTRI12H4BL



FEATURES

- Heavy-duty sealed bearings
- Steel mounting bracket for extra strength
- Corrosion resistant plywood blades
- Hang-sure mounting
- Summer and winter reversible action
- Colour selector switch
- Tough easy-to-clean powder coated finish
- Indoor use only

BOX CONTENTS

- Motor assembly with integrated LED Light
- 4-blades
- Mounting bracket
- Instruction sheet
- 2 x screws and lugs for bracket
- 3-speed fan controller
- 12 x screws for blades
- Cover plate and screws
- Glass diffuser

	Single Product (Qty 1)	
	Cat. No.	Barcode
	RCFTRI12H4WE	9321001506348
Hang-sure mounting Suitable for all ceiling types including raked ceilings up to a 20° angle	RCFTRI12H4BL	9321001506355
Summer and winter reversible action Colour selector switch		
1200mm diameter	>	
	•	
Integrated LED Light		

Fan Speed	RPM*	Power (Watts)
Low	100	13
Medium	160	26
High	225	50

*RPM: Rotations per Minute

Legrand - Australia 1300 369 777 www.hpm.com.au ABN 31 000 102 661