


DUCT, 100 mm x 100 mm x 2 m**Part number: TC1279-23****1. USE / APPLICATION**

The 100 mm duct carries up to 1100 pigtails or patch cords (2 mm dia) to a depth of 50 mm, without causing excess stress on them, during the removal processes. This duct is made of tough Noryl plastic with a non - halogen fire retardant. It connects to other 100 mm duct sections and various bends, adapters etc., using either: a standard joiner (Part No: TC1279-27) or a slotless joiner (Part No: TC1279-248A); that are available separately.

2. BENEFITS & FEATURES

- Clips straight into joiner
- Tough, fire retardant material
- Joiners (Part No's: TC1279-27 or TC1279-248A); available separately.
- Purchase by the unit

3. TECHNICAL ATTRIBUTES

Dimensions	120 mm (W) x 105 mm (H) x 2000 mm (D)
Weight	2.04 kg
Materials	Fire retardant plastic, Halogen free, UL94-VO rated
Colour	Yellow