

**ELBOW ASSEMBLY, INTERNAL LID, 90 DEGREES UP,
300 mm DUCT**

Part number: TC1279-298KIT

**1. USE / APPLICATION**

The 90 degree UP elbow is a 300 mm vertical lead off with an internal lid, so that cables within the elbow can be accessed. This is usually used where cables are to be installed vertically. This assembly is made up of: 2 x Part No: TC1279-283A and 1 x Part No: TC1279-287A. There are two 300 mm outlets, which use slotless joiners (Part No. TC1279-287A), that are available separately.

2. BENEFITS & FEATURES

- Provides fibre access and retrofit options
- Clips straight into joiner, Part No: TC1279-287A (one supplied)
- Includes covers: 2 x Part No: TC1279-284
- Ribs included for extra strength
- Tough fire retardant material
- Slotless Joiners (Part No: TC1279-287A), available separately
- Purchase by the unit

3. TECHNICAL ATTRIBUTES

| | |
|------------|---|
| Dimensions | 322 mm (W) x 135 mm (H) x 257 mm (D) |
| Weight | 730 grams |
| Materials | Fire retardant plastic, Halogen free, UL94-VO rated |