
La legrand[®]

87045 LIMOGES Cedex Telephone: 33 5 55 06 87 87 - Fax: 33 5 55 06 88 88

Céliane™

British standard (BS) socket outlets

Cat. No(s): 671 55




1. USE

Socket outlets to British standard.

2. RANGE

Designation	Cat. No.	Nbr. of modules	Connection method	Fixing method	Weight (g)	General characteristics
2P+E BS socket	671 55	2	with screws	with clips	35.5	13 A - 250 V~


3. INSTALLATION




- 1 Clip the front of the mechanism onto the support frame.
- 2 Clip the cover plate onto the mechanism.
- 3 Clip the plate onto the support frame.

The mechanism can be flush- or surface-mounted.

4. OVERALL DIMENSIONS





5. CONNECTION

Terminal type: with oblong slot Terminal capacity: 2 x 4 mm² Stripping length: 9 mm

6. OPERATION

Conventional operation by inserting or removing an industry-standard plug.

7. TECHNICAL DATA

7.1 Mechanical characteristics Impact resistance: IK 04 Penetration by solid/liquid bodies: IP 20

7.2 Material characteristics Mechanism: Polycarbonate Cover plate: Polycarbonate

7.3 Electrical characteristics Self-extinguishing: 850 °C / 30 s.

7.4 Climatic characteristics Storage temperature: -10 °C to +70 °C Operating temperature: - 5 °C to +50 °C

8. CONFORMITY AND APPROVALS

Approvals pending: ASTA BEAB