


87045 LIMOGES Cedex

Telephone: 33 5 55 06 87 87 - Fax: 33 5 55 06 88 88

Céliane™

Euro-US socket outlet

Cat. No(s): 671 51




1. USE

Socket outlet to Euro-US standard.

2. RANGE

Designation	Designation	Cat. Nos	Nbr. of modules	Connection method	Fixing method	Weight (g)	General characteristics
	Euro-US standard 2P socket	671 51	1	with screws	with clips	22.70	15A - 127V~ US socket 16A - 250V~ Euro socket


3. INSTALLATION



- 1 Clip the front of the mechanism onto the support frame.
- 2 Clip the cover plate onto the mechanism.
- 3 Clip the plate onto the support frame.

The mechanism can be flush or surface-mounted.

4. OVERALL DIMENSIONS



5. CONNECTION

Terminal type: saddle Terminal capacity: 2 x 4 mm² Stripping length: 9 mm

6. OPERATION

Conventional operation by inserting or removing an industry-standard plug.

7. TECHNICAL DATA

7.1 Mechanical characteristics

Impact resistance: IK 04

Penetration by solid/liquid bodies: IP 20

7.2 Material characteristics

Mechanism: Reinforced polycarbonate

Cover plate: Polycarbonate

7.3 Electrical characteristics

Mech. self-extinguishing properties: $850^{\circ}\text{C}/30~\text{s}$

7.4 Climatic characteristics

Storage temperature: -10°C to +70°C Operating temperature: -5°C to +50°C

Technical data sheet: F00816EN/00 Updated: Created: 08/09/2008