


87045 LIMOGES Cedex Telephone: 33 5 55 06 87 87 - Fax: 33 5 55 06 88 88

## Céliane™

# 8-contact telephone socket

## Cat. No(s): 673 38



### **1. USE**

Telephone socket fitted with an 8-contact jack connector. Accepts 6- or 8-contact jack connectors (see data sheet for Cat.

No. 512 38).


Compliant with France Telecom technical specifications no. ST - PAA -TPA - PRI 537.

Accepts plugs compliant with France Telecom technical specifications ST - PAA - TPA - PRI 537.

## 2. RANGE

 Designation	Cat. No.	weight (g)
8-contact telephone socket	67338	27g

### **3. OVERALL DIMENSIONS**



#### **1. USE**

- 1 Clip the rear of the mechanism onto the support frame.
- 2 Screw the mechanism / support frame assembly to the flush-mounting box.
- 3 Clip the rocker onto the mechanism.
- 4 Clip the plate onto the support frame.

Can be fitted with all Céliane finishes. Multi-gang horizontal or vertical mounting.

## 5. INSTALLATION


#### France Telecom authorisation for use

- Not authorised for claw-mounted support frame.
- For safety reasons, installing a telephone socket and a power socket outlet in the same box is prohibited.


#### France Telecom recommendations

- Install two sockets, one of which near to a power socket outlet.
- Position the sockets between 8 and 25 cm from the ground.
- The internal installation must be compatible with ISDN.

#### Case 1:



Case 2:




## Céliane<sup>™</sup> 8-contact telephone socket

Cat. No(s): 673 38


## 6. CONNECTION


#### 6.1 Socket connection



Wire sockets in parallel: all wires must be connected. Use France Telecom-approved 4-pair cable,  $\emptyset$  0.6 mm, type 278-4.6 Comply with the contact numbers and the wire colours.







## 7. TECHNICAL DATA

#### 7.1 Mechanical characteristics

Impact resistance: IK 04 Penetration by solid/liquid bodies: IP 41 (C15-100) \$ without rocker

#### 7.2 Material characteristics Base: Polycarbonate

**7.3 Electrical characteristics** Self-extinguishing: 650 °C / 30 s

**7.4 Climatic characteristics** Storage temperature: -10 °C to +70 °C Operating temperature: -5 °C to +50 °C

#### 8. CLEANING

No cleaning