
# La legrand®

128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex Tél. : 0 (+33) 5 55 06 87 87 - Fax : 0 (+33) 5 55 06 88 88 www.legrand.com

## Plexo™ Junction box ERP



#### 1.USE

Special weatherproof boxes for safety circuits in public buildings and work premises.

In accordance with regulations governing public buildings under Article EL 16 §1.

- Compliant with the NFS 61-937 standard dealing with fire safety systems including actuated fire safety devices (compartmentalization, smoke extraction, etc.).

- Cover colour grey RAL 7037.

- Box colour red RAL 3000.

- Can be fitted with IP2x terminal strips for the 155 x 110 box.

2. RANGE

Cat. No.	Inside dimensions	Nbr. of caps	Cover type
920 15	80 x 80 x 45	7	clippable
920 25	105 x 105 x 55	7	1/4 turn screw closing
920 45	155 x 110 x 74	10	1/4 turn screw closing

#### **3. INSTALLATION**

- Diameter of cables and tubes accepted:


• 4 to 20 mm for round and square boxes up to 80 x 80

• 4 to 25 mm for 105 x 105 square boxes

- Fixing with vertical level adjustment possible using Ø 5 mm max. screw
  Possible to fix outside the wiring space using Ø 4 mm screws for
- square boxes Cat. Nos. 0 920 25/45.
- Can be fixed using wall plug Cat. No. 0 319 57


- Can be fixed using SPIT «Pulsa 700 E» nail gun

- Marking areas on the cover for labelling the circuits on internal face and identifying the junction on external face.




## 3. INSTALLATION (continued)


- Removable cover linked with the box by a tie



- Installing cables and tubes < Ø 16 mm




- Installing Ø 20 and 25 mm tubes




## 3. INSTALLATION (suite)

\_ Specific installation in case of condensate drain:


Creation of drainage holes with a diameter of 6mm at the places indicated according to the direction of assembly.







## 4. DIMENSIONS (mm)

- Square box 80 x 80







- Square box 105 x 105





- Rectangular box 155 x 110





Created: 10/12/2008

#### **5. TECHNICAL CHARACTERISTICS**

#### ■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 55 Protection against impact: IK 07

#### 5.2 Material characteristics

Colour: Box red RAL 3000 Cover and end caps RAL 7037 Material: Box ABS Cover: PP (Polypropylene) Glands: SEBS

Halogen-free UV-resistant

Resistant to oil and grease

Self-extinguishing: 960° C / 5 s

## 5.3 Climate characteristics

Storage temperature: -25°C to +70°C Use temperature: -25°C to +45°C

## 6. CLEANING

Surface cleaning with a dry cloth or cloth soaked in soapy water. Do not use acetone, tar remover or trichlorethylene.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

#### 7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards. See e-catalogue.