




# Mosaic™

# **Antimicrobial\* plates for British standard**

Cat. No(s): 6 780 23/24/25/26







#### 1. USE

Plates for covering mechanisms.

Fixing with clips.

These products are made of silver-ion based antimicrobial\* material. This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical, destruction).


Particularly suitables for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc.) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc.).

These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

### 2. RANGE

| Designation                    | White    |
|--------------------------------|----------|
| IP 44 2 modules plate          | 6 780 24 |
| 1 module plate                 | 6 780 25 |
| 2 modules plate                | 6 780 26 |
| 2 x 2 modules horizontal plate | 6 780 23 |

# 3. DIMENSIONS (mm)



| Cat. Nos | Α  | В   | С   | D        | E    |
|----------|----|-----|-----|----------|------|
| 6 780 24 | 88 | 88  | -   | 45.5     | 45.5 |
| 6 780 25 | 92 | 88  | 8.5 | 23       | 45.5 |
| 6 780 26 | 92 | 88  | 8.5 | 45.5     | 45.5 |
| 6 780 23 | 92 | 150 | 8.5 | 2 x 45.5 |      |

# 4. TECHNICAL CHARACTERISTICS

#### ■ 4.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid/bodies and liquids: IP 44 for Cat. No. 6 780 24

# ■ 4.2 Material characteristics

Plate for Cat. Nos 6 780 23/25/26:

White PC RAL 9003 + antimicrobial\* treatment

Halogen-free

**UV-resistant** 

Sub-plate: opalescent PC

Plate end flap for Cat. No. 6 780 24: PP + antimicrobial\* treatment

Sub-plate: ABS + SEBS

Halogen-free

**UV-resistant** 

Self-extinguishing: 650°C/30 s

# ■ 4.3 Climate characteristics

Storage temperature: - 10°C to + 70°C Usage temperature: - 5°C to + 35°C

# **5. CLEANING**

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the cleaning products: Hexane (EN 60669-1, methylated spirit, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Resistance to type cleaning hospital: Anios, Surfanios, Bactilysine, Diluted hydrogen peroxide (35 %).

**Caution:** Always test before using other special cleaning products

Do not paint the plates.

# 6. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing. See e.catalogue.

\*Contains silver ions that limit the development of bacteria on the surface.