


128, av. du Maréchal-de-Lattre-de-Tassigny - 87045 LIMOGES Cedex - France
Tel: 0 (+33) 5 55 06 87 87 - Fax: 0 (+33) 5 55 06 88 88
www.legrand.com

Salbei™
Switches and multifunction switches

Cat. No(s): 7 671 00/01/02/03/04/06/08 - 7 672 00/01/02/03/04/06/08/66 - 7 673 00/01/02/03/04/06/08/66 7 674 00/01/02/03/04/06/08 - 7 675 00/01/02/03/04/06/08/66 - 7 676 00/01/02/03/04/06/08/66 7 677 00/01/02/03/04/06/08/66 - 7 678 00/01/02/03/04/06/08/66 - 7 679 00/01/02/03/04/06/08/66


7 671 00


7 671 02


7 671 03


1. USE


Control mechanisms supplied with rockers and support frames.
To be fitted with one-gang or multi-gang plates.
Flush or surface mounting.
Fixing with screws and/or claws.

2. RANGE

Description	White	Aluminium	Anthracite	Ivory	Champagne	Matt Gold	Pink	Smoked Grey	White Pearl
One-way switch	7 671 00	7 672 00	7 673 00	7 674 00	7 675 00	7 676 00	7 677 00	7 678 00	7 679 00
Two-way switch	7 671 01	7 672 01	7 673 01	7 674 01	7 675 01	7 676 01	7 677 01	7 678 01	7 679 01
Double two-way switch	7 671 02	7 672 02	7 673 02	7 674 02	7 675 02	7 676 02	7 677 02	7 678 02	7 679 02
Three one-way switch	7 671 03	7 672 03	7 673 03	7 674 03	7 675 03	7 676 03	7 677 03	7 678 03	7 679 03
Intermediate switch	7 671 04	7 672 04	7 673 04	7 674 04	7 675 04	7 676 04	7 677 04	7 678 04	7 679 04
Double one-way switch	7 671 06	7 672 06	7 673 06	7 674 06	7 675 06	7 676 06	7 677 06	7 678 06	7 679 06
Illuminated one-way switch	-	7 672 66	7 673 66	-	7 675 66	7 676 66	7 677 66	7 678 66	7 679 66
Illuinated two-way switch	7 671 08	7 672 08	7 673 08	7 674 08	7 675 08	7 676 08	7 677 08	7 678 08	7 679 08

3. OVERALL DIMENSIONS (mm)





A	B	C	D
76	76	45.5	14.5

4. CONNECTION

Screw terminals:
Terminal capacity: 2 x 2.5 mm^2
Stripping length: 10 mm for Cat. Nos 7 67x 03/04

Automatic terminals:
Terminal capacity: 2 x 2.5 mm^2
Stripping length: 13 mm for Cat. Nos 7 67x 00/01/02/06/07/08/66

Compatible with flexible or rigid cables.
Cable entries for the phase marked with red colour code.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics
Impact tests: IK 04
Penetration by solid bodies/liquids: IP 20.

■ 5.2 Material characteristics
Rocker: ABS
Mechanism housing: PC
Halogen free
UV resistant
Claws: steel

Material of the support:
- Cat. Nos 7 67x 00/01/02/06/08/66: PC Grey RAL 7037
- Cat. Nos 7 67x 03/04: PC Grey RAL 7037 + 10 % glass fiber

Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place.
+ 650° C / 30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics
Voltage: 250 V~
Current: 10 AX
Frequency: 50/60 Hz

■ 5.4 Climatic characteristics
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

6. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following cleaning substances:
Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
See e.catalogue.